RoHs

VER	MARK	PR. BY	DESCRIPTTON	DATE









RECOMMEND P.C.B LAYOUT
PCB TOLERANCE:±0.05 (TOP VIEW)

SPECIFICATIONS
Current Rating: 1.0 Amps
Withstanding Voltage:AC 500V
Insulation Resistance:1000MΩ Min
Contact Resistance:20mΩ Max
Operation Temperature:-40° to+105°
Insrlator Material:Polyester(UL94V-0)
Contact Material:Phosphor bronze
Standard:PA6T
Contact Plating:Gold Flash
Max.Processing Temp:240° C for30-60seconds
(260° C for5seconds)

P/N	PIN	DIM.A	DIM.B
HMT-PM1.27-2-2PL	2*2	1.27	2.54
HMT-PM1.27-2-3PL	2*3	2.54	3.81
HMT-PM1.27-2-4PL	2*4	3.81	5.08
HMT-PM1.27-2-5PL	2*5	5.08	6.35
HMT-PM1.27-2-6PL	2*6	6.35	7.62
HMT-PM1.27-2-7PL	2*7	7.62	8.89
HMT-PM1.27-2-8PL	2*8	8.89	10.16
HMT-PM1.27-2-9PL	2*9	10.16	11.43
.....	.....	.....	.....
HMT-PM1.27-2-50PL	2*50	(PIN-1)x1.27	(PIN)x1.27

GENERAL TOLERANCES UNLESS SPECIFIED		深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd		
X.° ±0.30	X.° ±5°	PART NO. HMT-PM1.27-2-NPL	TITLE: 1.27FH H4.3 2xNPin SMT U型 PC4.8 PB4.6 6T	
X.X° ±0.20	X.X° ±1°			
X.XX°±0.10	X.XX°±0.5°	DESIGN: James	CUSTOMER	SIZE: A4 / UNITS: MM
MANUFACTURE DWG		CHED: Talen		SCALE: N:A / SHEET: 1/1
		APPD: Sophia		