

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2026.04.14	
/	/		/	/	/

PART NO.:

X02 15 F I 17 B 5

Series NO.

Row No.Pin No.XX-15

Welding Board Angle :F-Female

T Tradutlional

Planting Categoty: 17:AU SW

Color:B-BLACK

5:TYPE-5;

Specifications()

- 1.Voltage rating():DC 1000V
 - 2.Current rating():3A AC/DC
 - 3.Withstanding voltage():≥1000V AC/minute
 - 4.Insulation resistance():≥5000MΩ Min
 - 5.Contact resistance():≤30mΩ Max
 - 6.Mating cycles 5000 cycles Min
 - 7.Insertion force ≥5.1Kg.f
 - 8.extraction force ≤1.5Kg.f
 - 9.retention ≤1.0Kg.fpin
 - 10.Temperature range():-25 ~+80
- Material

1.Rubber core:PBT UL94V-0

PBT UL94V-0


2.The iron shell:SPCC Tin Plating/Gold Plating

SPCC, /

3.Terminal C5191

C5191

TYPE-5:



AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAUCES	



DESIGN		VIEW:		MODEL TYPE:	D-SUB
CHECKED		UNIT:	mm/in	PART NO.:	X0215FT17B5
APPROVED		SIZE:	A4	DWG NO.:	

XKB INDUSTRIAL PRECISION CO.,LIMITED

SCALE	PAGE	REVISION
N/A	1/1	A0