



Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:1A AC/DC

额定电流: 1A AC/DC

Withstanding voltage:500V AC/minute

耐受电压：500V AC/分钟

Temperature range:-40°C-+105°C

温度范围:  $-40^{\circ}\text{C}$ ~ $+105^{\circ}\text{C}$

Insulation resistance: 1000MΩ min

绝缘电阻: 1000MΩ Min

Contact resistance:20mΩ Max

接触电阻: 20mΩ Max

X2001 W V - 2x30 A - 6T V01

① ② ③ ④ ⑤ ⑥ ⑦

1.Series No

## 2. Category: W-Wafer

### 3.Welding Board Angle:V-Stright 180°

4.Row No.Pin No:2xXX-2x03-2x30P

5. Category: A-No gap

6.Material:6T-Nylon 6T UL94V-0

### 7.Plating:V01-Gold Flash

| Poles | Dimensions |       | Poles | Dimensions |       |
|-------|------------|-------|-------|------------|-------|
|       | A          | B     |       | A          | B     |
| 2x03  | 4.00       | 13.30 | 2x12  | 22.00      | 31.30 |
| 2x04  | 6.00       | 15.30 | 2x13  | 24.00      | 33.30 |
| 2x05  | 8.00       | 17.30 | 2x15  | 28.00      | 37.30 |
| 2x06  | 10.00      | 19.30 | 2x17  | 32.00      | 41.30 |
| 2x07  | 12.00      | 21.30 | 2x18  | 34.00      | 43.30 |
| 2x08  | 14.00      | 23.30 | 2x20  | 38.00      | 47.30 |
| 2x09  | 16.00      | 25.30 | 2x22  | 42.00      | 51.30 |
| 2x10  | 18.00      | 27.30 | 2x25  | 48.00      | 57.30 |
| 2x11  | 20.00      | 29.30 | 2x30  | 58.00      | 67.30 |

|                     |          |               |                  |
|---------------------|----------|---------------|------------------|
| X2001WV-2x30A-6TV01 | Nylon 6T | Brass         | X2001HA-2x30     |
|                     |          |               | X2001HA2-2x30    |
| PART NO             | Material | Material(Pin) | Suitable XKB IDC |

|                                               |             |      |         |          |                        |      |
|-----------------------------------------------|-------------|------|---------|----------|------------------------|------|
|                                               |             |      |         |          | ANGLAR                 | ±5°  |
| Δ x                                           |             |      |         |          | L ≤ 4                  | ±0.2 |
| Δ x                                           |             |      |         |          | 4 < L ≤ 16             | ±0.3 |
| Δ x                                           |             |      |         |          | 16 < L ≤ 63            | ±0.4 |
| MARK                                          | DESCRIPTION | DATE | REVISED | APPROVED | L > 63                 | ±0.5 |
| REVISIONS                                     |             |      |         |          | UNSPECIFIED TOLERANCES |      |
| www.helloxkb.com www.helloxkb.cn www.xk-da.cn |             |      |         |          |                        |      |



XKB INDUSTRIAL PRECISION CO.,LIMITED

|                       |  |                                                                                             |                                     |              |                |
|-----------------------|--|---------------------------------------------------------------------------------------------|-------------------------------------|--------------|----------------|
| DSND                  |  | SCALE: N/A                                                                                  | MODEL TYPE:<br>2.0mm Jane cattle 筒牛 |              |                |
| DWN                   |  | VIEW:  | PART NO.:<br>X2001WV-2x30A-6TV01    |              |                |
| CHKD                  |  | UNIT: mm/in                                                                                 | DWG NO.:<br>X-X2001WV-2x30A-6TV01   |              |                |
| APPD                  |  | SIZE: A4                                                                                    |                                     |              |                |
| PRECISION CO.,LIMITED |  |                                                                                             | WEIGHT                              | SHEET<br>1/1 | REVISION<br>A0 |