






|      |           |          |                 |            |        |
|------|-----------|----------|-----------------|------------|--------|
|      | REVISIONS |          |                 |            |        |
| REV. | ECN NO.   | LOCATION | DESCRIPTION     | DATE       | DESIGN |
| A0   | N/A       |          | INITIAL RELEASE | /          | /      |
| A1   | N/A       |          | 图面升级整理图面        | 2025.12.22 | 阿树     |




## ■ SPECIFICATIONS

- Voltage rating: 600V AC/DC
- Current rating: 9A AC/DC
- Withstanding Voltage: 1500V AC/minute
- Temperature range: -45°C +125°C
- Insulation resistance:  $\geq 1000\text{M}\Omega$
- Contact resistance:  $\leq 30\text{m}\Omega$
- After environmental testing:  $\leq 20\text{m}\Omega$

PART NO.:

X9357 W R-2x09 S-NO SN XX  
 (1) (2) (3) (4) (5) (6) (7) (8)

- ① Series No
- ② Category:W-Wafer
- ③ Welding Board angle:R-Stright 90°
- ④ Row No.Pin No:2xXX-2x01P~2x12P
- ⑤ Special NO.:S-With positioning column
- ⑥ Material:N2-PA6694V-2;  
N0-PA6694V-0
- ⑦ Plating:SN-Bright tin plating
- ⑧ Color: Blank-natural color  
BK-Black BL-BLUE RE-RED



| Poles | Dimensions(mm) |       |
|-------|----------------|-------|
|       | A              | B     |
| 2x01  | ---            | 5.40  |
| 2x02  | 4.20           | 9.60  |
| 2x03  | 8.40           | 13.80 |
| 2x04  | 12.60          | 18.00 |
| 2x05  | 16.80          | 22.20 |
| 2x06  | 21.00          | 26.40 |
| 2x07  | 25.20          | 30.60 |
| 2x08  | 29.40          | 34.80 |
| 2x09  | 33.60          | 39.00 |
| 2x10  | 37.80          | 43.20 |
| 2x11  | 42.00          | 47.40 |
| 2x12  | 46.20          | 51.60 |

|                    |                   |              |             |                       |
|--------------------|-------------------|--------------|-------------|-----------------------|
| X9357WR-2x09S-N0SN | Nylon 66 UL 94V-0 | Brass        | Tin- Plated | X9357H                |
| X9357WR-2xXS-N2SN  | Nylon 66 UL 94V-2 |              |             |                       |
| PART NO            | Material          | Matenal(Pin) | Finlsh(Pin) | Suitable XKB Terminal |

|             |               |
|-------------|---------------|
| AuGLAR      | $\pm 5^\circ$ |
| X.          | $\pm 0.40$    |
| X.x         | $\pm 0.30$    |
| X.xx        | $\pm 0.20$    |
| X.xxx       | $\pm 0.15$    |
| UNSPECIFIED | TOLERAUCES    |

XKLB 星城 Connection

|          |    |                                                                                             |                                              |
|----------|----|---------------------------------------------------------------------------------------------|----------------------------------------------|
| DESIGN   | 阿树 | VIEW:  | MODEL TYPE:<br>4.20 mm Crimp Style Connector |
| CHECKED  |    | UNIT: mm/in                                                                                 | PART NO.:<br>X9357WR-2x09S-N0SN              |
| APPROVED |    | SIZE: A4                                                                                    | DWG NO.:                                     |

|       |      |          |
|-------|------|----------|
| SCALE | PAGE | REVISION |
| N/A   | 1/1  | A1       |