



CHIP COMMON MODE CHOKE


High Common Mode Impedance at High Frequency.
Excellent Noise Suppression Performance.
Small Size and Low Profile, Surface Mount Type.
Operating Temperature Range: -40°C to $+85^{\circ}\text{C}$.
RoHS Compliant.



Electrical Specifications @25°C


Part Number	Common mode Impedance (ohm $\pm 25\%$ @100M)	DCR (Ω Max)	Rated Current mA Max	Rated Volt (Vdc)	IR M(Ω Min)
ACM2012-900-2P-T002 T-CND	90	0.19	400	50	10
ACM2012-121-2P-T002 T-CND	120	0.22	370	50	10
ACM2012-201-2P-T002 T-CND	200	0.25	350	50	10
ACM2012-361-2P-T002 T-CND	360	0.50	220	50	10
ACM2012-202-2P-T002 T-CND	2000	2.50	150	50	10

MECHANICAL



Unless otherwise specified all tolerances are: $\pm 0.25\text{mm}$


TAPING AND PACKING



Quantity (pcs):
2000 PCS PER REEL
10 REELS PER CARTON
20000 PCS PER CARTON


Dimensions in mm

SCHEMATICS




• No polarity

IMPEDEANCE FREQUENCY



Reel



Dimensions in mm