










PCB WELDING DIMENSIONS



SPECIFICATION
1. Rating: DC 20V 50mA
2. Contact resistance: 1Ω Max.
3. Insulation resistance: 100MΩ Min, 100V/min
4. Dielectric strength: 100V AC/min
5. Operating force: 50gf Max.
6. Operating life: 100,000 cycles
7. Operating temp: -10℃ to +60℃
8. Storage temp: -20℃ to +70℃

④	TERMINAL	—	1	PHOSPHOR	Ag plating	—
③	HOUSING	—	1	PA	BLACK	—
②	CONTACT	—	1	SUS	Ag plating	—
①	STEM	—	1	LCP	BLACK	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS			DATE				
DRAWN	LIANG		2026.03.12				
CHECKED					TITLE:	DETECTION SWITCH	
APPROVALS					PART NO.	K5-1666SA-02	
TOLERANCES ARE	30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ: 	
	10~30	±0.20					
	5~10	±0.15					
	~ 5	±0.10					
			±2'	DRAWING NO.	_____	SHEET 1 OF 1	

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			