





Poles	Dlmenstions(mm) A
2*02	5.08
2*03	7.62
2*04	10.16
2*05	12.70
2*06	15.24
2*07	17.78
2*08	20.32
2*09	22.86
2*10	25.40
2*12	30.48
2*14	35.56
2*16	40.64
2*20	50.80
2*21	53.34
2*24	60.96
2*25	63.50



Recommended P.C.B
Layout(±0.05)



Technical Data
Pin(outer sleeve):Brass,machined CuZn38Pb2
Insulator:PPS UL94V-0 colour:black
Current rating:3Amps
Mating pin Ø:0.60/0.48mm
Mechanical life:min 500cycles
Contact resistance:max 10m Ω
Dielectric strength:min 1000V RMS
Operating temperature:-40°C to+105°C
Soldering temperature:+255°C

X5621 W V-2x04-C762 D1196-1196

- ① ② ③ ④ ⑤ ⑥ ⑦

- ① Series.N0.
② Category : W-Wafer
③ Welding Board Angle : V-Straight 180°
④ Row No-Pin No:2*XX-03,04,05,06,07,08,09,10,12,14,16 20,21,24,25
⑤ Plastic Height :C=7.62mm
⑥ Pin Length :D:1196=11.96mm;1000=10.0mm;1220=12.20mm;
⑦ 1196-Type1196

X5621WV-2x04-C762D1196-1196	PPS 94V-0	Brass	Tin Gold 1u"	X5621F
PART N0	Material	Material(Terminal)	Finish(Terminal)	Mates With XKB Pin Header

							DSND		DATE		SCALE: N/A	MODEL TYPE: 2.54mm BTB Style Connector			
					ANGLAR	±5°	DWN		DATE		VIEW: 	PART NO.: X5621WV-2x04-C762D1196-1196			
ΔX					L ≤ 4	±0.2	CHKD		DATE		UNIT: mm/in	DWG NO.: X-X5621WV-2x04-C762D1196-1196			
ΔX					4 < L ≤ 16	±0.3	APPD		DATE		SIZE: A4				
ΔX					16 < L ≤ 63	±0.4									
MARK	DESCRIPTION			DATE	REVISED	APPROVED	L > 63	±0.5							
REVISIONS							UNSPECIFIED TOLERANCES		XKB INDUSTRIAL PRECISION CO.,LIMITED				WEIGHT	SHEET	REVISION
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn													1.0g	1/1	A0