





技术指标:

- 1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象.
- 2. 温度范围: $-40^{\circ}\text{C} \sim 105^{\circ}\text{C}$ (含通电时的温度上升值).
- 3. 额定电压: 30V, AC/DC.
- 4. 接触电阻: 初期 $\leq 0.02\ \Omega$, 环境试验后 $\leq 0.04\ \Omega$.
- 5. 绝缘电阻: $\geq 100\text{M}\ \Omega\ \text{min.}$
- 6. 额定电流: 0.5A, AC/DC
(使用AWG#32, 0. D0. $38 \pm 0.02\text{mm}$).
- 7. 耐电压: AC 200V/1分钟.

序号	品名	材质
1	0.8-C型WTB 刺破型公头胶芯	LCP UL94 V-0 米黄色
2	0.8-C型WTB 刺破型公头端子	铜合金 / 镀金

Part No	CKT	A	B	C	D
HMT-0.8-2P-JK-A2	2	0.80	1.78	2.18	2.40
HMT-0.8-3P-JK-A2	3	1.60	2.58	2.98	3.20
HMT-0.8-4P-JK-A2	4	2.40	3.38	3.78	4.00
HMT-0.8-5P-JK-A2	5	3.20	4.18	4.58	4.80
HMT-0.8-6P-JK-A2	6	4.00	4.98	5.38	5.60
HMT-0.8-7P-JK-A2	7	4.80	5.78	6.18	6.40
HMT-0.8-8P-JK-A2	8	5.60	6.58	6.98	7.20
HMT-0.8-9P-JK-A2	9	6.40	7.38	7.78	8.00
HMT-0.8-10P-JK-A2	10	7.20	8.18	8.58	8.80
HMT-0.8-11P-JK-A2	11	8.00	8.98	9.38	9.60
HMT-0.8-12P-JK-A2	12	8.80	9.78	10.18	10.40
HMT-0.8-13P-JK-A2	13	9.60	10.58	10.98	11.20
HMT-0.8-14P-JK-A2	14	10.40	11.38	11.78	12.00
HMT-0.8-15P-JK-A2	15	11.20	12.18	12.58	12.80
HMT-0.8-16P-JK-A2	16	12.00	12.98	13.38	13.60
HMT-0.8-17P-JK-A2	17	12.80	13.78	14.18	14.40
HMT-0.8-18P-JK-A2	18	13.60	14.58	14.98	15.20
HMT-0.8-19P-JK-A2	19	14.40	15.38	15.78	16.00
HMT-0.8-20P-JK-A2	20	15.20	16.18	16.58	16.80

GENERAL TOLERANCES UNLESS SPECIFIED		 HMTconn 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd	
X. ± 0.50	$\pm 1^{\circ}$	PART NO. HMT-0.8-NP-JK-A2	TITLE: 0.80 Pitch C型WTB刺破公头
.X ± 0.20		DESIGN: James	CUSTOMER
.XX ± 0.10		CHED: Talen	SIZE A4
MANUFACTURE DWG		APPD: Sophia	UNITS MM
			SCALE N:A
			SHEET 1/1