







电气性能

NOTES:

- MATERIAL:
 - HOUSING: PA46. COLOR IS BLACK;
 - CONTACT: PHOSPHOR COPPER (C5191,T=0.25);
- ELECTRICAL:
 - VOLTAGE RATING: 30 VAC RMS;
 - CURRENT RATING: 0.5 AMP;
 - CONTACT RESISTANCE: 30MILLIOHMS MAX.;
 - WITHSTAND VOLTAGE: 500 VAC RMS
50(60)Hz,1MIN.;
 - INSULATION RESISTANCE: 100MEGOHMS MIN
@500V DC;
- MECHANICAL:
 - MATING FORCE: 5~25N;
 - UNMATING FORCE: 5~25N;
 - OPERATING LIFE: 5000 CYCLES;
- PLATING:
 - TERMINAL:
NI PLATING OVER ALL,
TIN PLATING ON SOLDER AREA,
- ENVIRONMENTAL:
 - STORAGE TEMPERATURE RANGE: -40°C~+85°C;
 - OPERATION TEMPERATURE RANGE: -25°C~+70°C;
- SALT SPRAY TEST:8H(EXCLUDING RIVETED BENDS)

序号	品名	材质	电镀/颜色	备注
A	基座	PA46	黑色	
B	端子	C5191	焊区镀锡 全周镀镍	

			GENERAL TOLERANCE		制 图	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM	TOL	DRAWING				
					审 核				
			X. X	±0.30	CHECK				
			X. XX	±0.20	批 准	产品名称	313耳机四节 弯脚6.8 黑色	版本	A
			X. XXX	±0.10	APPROVAL	产品料号	HC-PJ-3134-6P-D	REV.	
			Angle	±3.0°	SCALE	PART NO.		单 位	mm
序号	变更内容	日期			投 影	材料		页 次	1/1
No.	MODIFY CONTENT	MODIFY DATE			Projection	MATERIAL		SHEET	