



1.Features

- $V_{DS(V)}=650V$
- $I_D=7A$
- $R_{DS(ON)}\leq 1.4\Omega(V_{GS}=10V)$

2.Pinning information

Pin	Symbol	Description
1	G	GATE
2	D	DRAIN
3	S	SOURCE



3.Absolute Maximum Ratings $T_c=25^{\circ}C$

Parameter		Symbol	Rating	Units
Drain-source Voltage		V_{DS}	650	V
gate-source Voltage		V_{GS}	± 30	V
Continuous Drain Current	$T_c=25^{\circ}C$	I_D	7	A
Continuous Drain Current	$T_c=100^{\circ}C$	I_D	3.2	A
Drain Current – Pulsed ①		I_{DM}	28	A
Power Dissipation	TO-220F	P_D	83	W
Junction Temperature		T_J	150	$^{\circ}C$
Storage Temperature		T_{STG}	-55 to 150	$^{\circ}C$
Single Pulse Avalanche Energy ②		E_{AS}	230	mJ



4.Thermal resistance rating

Parameter	Symbol	MAX			Units
		TO-220	TO-220F	TO-262/263	
Thermal Resistance Junction-case	R_{thJC}	0.88	3.13	0.88	°C/W
Thermal Resistance Junction-ambient	R_{thJA}	62.5	62.5	62.5	°C/W



5. Electrical Characteristic ($T_c=25^\circ\text{C}$ unless otherwise noted)

Parameter	Symbol	Conditions	Min	Typ	Max	Units
Drain-source Breakdown Voltage	BV_{DSS}	$V_{GS}=0V, I_D=250\mu A$	650			V
Breakdown Voltage Temperature Coefficient	$\frac{\Delta BV_{DSS}}{\Delta T_J}$	$I_D=250\mu A$ Referenced to 25°C		0.8		$V/^\circ\text{C}$
Gate Threshold Voltage	$V_{GS(th)}$	$V_{DS}=V_{GS}, I_D=250\mu A$	2		4	V
Drain-source Leakage Current	I_{DSS}	$V_{DS}=650V, V_{GS}=0V, T_J=25^\circ\text{C}$			1	μA
		$V_{DS}=520V, V_{GS}=0V, T_J=125^\circ\text{C}$			10	μA
Forward Transconductance	g_{fs}	$V_{DS}=40V, I_D=3.5A$ ③		3		S
Gate-body Leakage Current ($V_{DS}=0$)	I_{GSS}	$V_{GS}=\pm 30V$			± 100	nA
Static Drain-source On Resistance	$R_{DS(on)}$	$V_{GS}=10V, I_D=3.5A$ ③		1.1	1.4	Ω
Input capacitance	C_{iss}	$V_{GS}=0V, V_{DS}=25V, f=1\text{MHz}$		955		pF
Turn -Off Delay Time	$t_{D(off)}$	$V_{DD}=325V, I_D=7A, R_G=25\Omega$ ③		90		ns
Total Gate Charge	Q_g	$I_D=7A, V_{DS}=520V, V_{GS}=10V$ ③		28		nC
Gate-to-Source Charge	Q_{gs}			7		nC
Gate-to-Drain Charge	Q_{gd}			12		nC
Continuous Diode Forward Current	I_S				7	A
Diode Forward Voltage	V_{SD}	$T_J=25^\circ\text{C}, I_S=7A, V_{GS}=0V$ ③			1.4	V
Reverse Recovery Time	t_{rr}	$T_J=25^\circ\text{C}, I_F=7A$		400		ns
Reverse Recovery Charge	Q_{rr}	$di/dt=100A/\mu s$ ③		3.3		μC
Output Capacitors	C_{oss}	$V_{GS}=0V, V_{DS}=25V, f=1\text{MHz}$		120		pF
Reverse transmission capacitance	C_{rss}			11.3		pF

Notes:


① Repetitive rating: Pulse width limited by maximum junction temperature.

② Starting $T_J=25^\circ\text{C}$, $V_{DD}=50V$, $L=10\text{mH}$, $R_G=25\Omega$, $I_{AS}=7A$.

③ Pulse Test : Pulse width $\leq 300\mu s$, Duty cycle $\leq 2\%$.



6.1 Typical characteristic





6.2Typical characteristic





Figure 9: Maximum Safe Operating Area



7.1 TO-220 Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A	A1	A2	A3	B	B1	C	C1	D	E	F	G
Min	9.7	8.44	1.05	4.8	15.4	12.9	4.28	1.1	0.6	3.4	2.65	5.2
Max	10.3	8.84	1.25	5.2	16.2	13.5	4.68	1.5	1.0	3.8	3.25	5.8

Symbol	H	K	L	L1	M	N	P	Q	T	DIA
Min	0.4	2.9	12.8	2.7	1.15	2.49	2.1	8.7	W:0.35	⌀1.5
Max	0.6	3.3	13.6	3.3	1.35	2.59	2.7	9.3		(deep 0.2)



7.2 TO-220 Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A	B	C	C2	C3	D	E	G	H	L2	L3
Min	4.30	0.60	0.28	1.17	2.30	8.80	9.80	2.44	28.55	1.10	2.59
Max	4.70	1.00	0.48	1.37	2.70	9.20	10.20	2.64	29.15	1.50	2.89



7.3 TO-220F Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A	A1	A2	b	c	D	E	E1	Φ	e	e1	L
Min	10.00	28.80	6.58	9.12	12.95	2.54	1.15	0.75	3.13	4.50	2.40	2.50
Max	10.20	29.20	6.78	9.32	13.25		1.25	0.85	3.23	4.70	2.60	2.70

Symbol	H
Min	0.45
Max	0.55



7.4 TO-263 Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A	a	B	b1	b2	H	h	h1	h2	h3	h4	L	L1	L2	L3
Min	9.6	7.2	4.3	1.25	2.2	15.2	1.34	10.3	9.1	1.34	2.5	2.2	1.2	0.7	1.2
Max	10.0	7.6	4.7	1.35	2.6	15.8	1.74	10.7	9.3	1.74	2.9	2.6	1.4	0.9	1.4

Symbol	L4	N
Min	0.4	2.4
Max	0.6	2.5



7.5 TO-252 Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A1	A2	A3	b	c	D	D1	D2	E	E1	E2	e	L1	L2	L3	θ
Min	0.00	2.18	0.90	0.65	0.46	6.35	4.95	4.32	9.40	5.97	5.21	2.286 BSC	0.89	1.70	0.60	0.00
Max	0.13	2.39	1.10	0.85	0.61	6.73	5.46	4.90	10.41	6.22	5.38		1.27	1.90	1.00	8.00



8.Ordering Information



Order Code	Marking	Package	Base QTY	Delivery Mode
UMW 7N65L	7N65L	TO-252	2500	Tape and reel
UMW 7N65F	7N65F	TO-220F	1000	Tape and box
UMW 7N65	7N65	TO-263	800	Tape and reel
UMW 7N65	7N65	TO-220	1000	Tape and box



9.Disclaimer

UMW reserves the right to make changes to all products, specifications. Customers should obtain the latest version of product documentation and verify the completeness and currency of the information before placing an order.

When applying our products, please do not exceed the maximum rated values, as this may affect the reliability of the entire system. Under certain conditions, any semiconductor product may experience faults or failures. Buyers are responsible for adhering to safety standards and implementing safety measures during system design, prototyping, and manufacturing when using our products to prevent potential failure risks that could lead to personal injury or property damage.

Unless explicitly stated in writing, UMW products are not intended for use in medical, life-saving, or life-sustaining applications, nor for any other applications where product failure could result in personal injury or death. If customers use or sell the product for such applications without explicit authorization, they assume all associated risks.

When reselling, applying, or exporting, please comply with export control laws and regulations of China, the United States, the United Kingdom, the European Union, and other relevant countries, regions, and international organizations.

This document and any actions by UMW do not grant any intellectual property rights, whether express or implied, by estoppel or otherwise. The product names and marks mentioned herein may be trademarks of their respective owners.