




This document contains proprietary information and such information may not be disclosed to others for any purposes, not used for sales/marketing/procurement purposes without written permission

REV	DESCRIPTION OF REVISION	ECN NO.	BY	DATE	APPROVED
A	Initial Release	—	H.wei	19/03/17	19/03/17



Mounting Hole



1 Electrical

- 1.1 Impedance 50 Ω
- 1.2 Frequency DC~6GHz
- 1.2 Dielectric withstanding voltage 1000V(volts RMS)
- 1.3 Center contact resistance $\leq 3m\Omega$
- 1.4 Outer contact resistance $\leq 2m\Omega$
- 1.5 Insulation resistance: $\geq 5000M\Omega$
- 1.6 VSWR 1.2max

2 Environmental&Mechanical


- 2.1 Temperature range -45℃~85℃
- 2.2 RoHs Compliant
- 2.3 Durability >500 cycles

3 Materials&plating

- 3.1 Body: Brass, Suco-Plated
- 3.2 Insulator: Teflon
- 3.3 Contact Pin: Beryllium-copper, Gold plated

Notes:

- 1. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE NOTICE AT ANY TIME
- 2. CUSTOMER OUTLINE DRAWING FOR REFERENCE ONLY

DRAWN: H.wei 19/03/17	TITLE: RF Coaxial Connector RF Connector SMA Female Flange Mount	 成都恒利泰科技有限公司 Chengdu HenryTech Technology co., Ltd			
ENGINEER: L.yu 19/03/17					
APPROVED: W.yi 19/03/17		 DIMENSION IN MILLIMETERS (mm)			
TOLERANCES UNLESS OTHERWISE SPECIFIED: X ± 0.50 .X ± 0.20 .XX ± 0.10 ANGLES $\pm 1^\circ$	PART NO: HL-SMA-KFD1034-1	SIZE: A4	SCALE: N/A	SHEET: 1/1	REV: A