

1

2

3



4

REVISIONS

REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	N/A		图框升级整理图面	2024.08.06	阿 树


A

A




B

B



P.C.B. RECOMMENDED LAYOUT



■SPECIFICATIONS

- Voltage rating:600V AC/DC
- Current rating:9A AC/DC
- Withstanding Voltage:1500V AC/minute
- Temperature range:-45°C+125°C
- Insulation resistance:≥1000MΩ
- Contact resistance:≤10mΩ
- After environmental testing:≤20mΩ

PART NO.:

X9357 W V-2x04 HN-N0 SN
① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- ① Series No
② Category:W-Wafer
③ Welding Board Angle:V-Straight 180°
④ Row No-Pin No: 2xXX-2x01P~2x12P
⑤ Plug the Pin&Specal NO.:HN-The hollow needle
⑥ Material:NO-PA66 94V-0;
⑦ Planting Category:SN-Bright tin plating
⑧ Color:Blank-natural color;

C

C

Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
2x01	—	5.40	2x07	25.20	30.60
2x02	4.20	9.60	2x08	29.40	34.80
2x03	8.40	13.80	2x09	33.60	39.00
2x04	12.60	18.00	2x10	37.80	43.20
2x05	16.80	22.20	2x11	42.00	47.40
2x06	21.00	26.40	2x12	46.20	51.60

D

D

ANGULAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	

XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED

X9357WV-2x04HN-N0SN	Nylon 66 UL 94V-0	Brass	Tin-Plated	X9357H
PARE NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB Housing
DESIGN	阿 树	VIEW:	MODEL TYPE: 4.20 mm Crimp Style Connectors	
CHECKED		UNIT: mm/in	PART NO.: X9357WV-2x04HN-N0SN	
APPROVED		SIZE: A4	DWG NO.: X-X9357WV-2x04HN-N0SN	
SCALE	PAGE	REVISION		
N/A	1/1	A1		

1

2

3

4