

PRIMARY CHARACTERISTICS


VCEO	IC	VCE(sat)	fT	Tjmax
-60V	-600mA	-1.60V	200MHz	150°C

Features

- Complementary to MMBT2222A
- Power Dissipation of 250mW
- High Stability and High Reliability
- RoHS Compliant and Halogen Free
- PNP Transistor in SOT-23 Package
- Marking: 2F

Mechanical Data

- Package: SOT-23 Small Outline Plastic Package
- Epoxy UL: 94V-0
- Mounting Position: Any
- Surface Mount Device


Absolute Maximum Ratings (Ta=25°C unless otherwise noted)



Parameters	Symbols	Limits	Units
Collector-Base Voltage	VCBO	-60	V
Collector-Emitter Voltage	VCEO	-60	V
Emitter -Base Voltage	VEBO	-5	V
Collector Current-Continuous	IC	-600	mA
Collector Power Dissipation	PC	250	mW
Junction Temperature	Tj	150	°C
Storage Temperature	Tstg	-55~+150	°C
Thermal resistance From junction to ambient	RθJA	500	°C/W






Electrical Characteristics(Ta=25°C unless otherwise noted)

Parameter	Symbol	Conditions	Min	Typ	Max	Unit
Collector-base breakdown voltage	V(BR)CBO	IC=-100μA, IE=0	-60	-	-	V
Collector-emitter breakdown voltage	V(BR)CEO	IC=-1mA, IB=0	-60	-	-	V
Emitter-base breakdown voltage	V(BR)EBO	IE=-10μA, IC=0	-5	-	-	V
Collector cut-off current	ICBO	VCB=-50V, IE=0	-	-	-20	nA
Emitter cut-off current	IEBO	VEB=-3V, IC=0	-	-	-10	nA
DC current gain	hFE(1)	VCE=-10V, IC=-150mA	100	-	300	
	hFE(2)	VCE=-10V, IC=-0.1mA	75	-	-	
	hFE(3)	VCE=-10V, IC=-1mA	100	-	-	
	hFE(4)	VCE=-10V, IC=-10mA	100	-	-	
Collector-emitter saturation voltage	VCE(sat)	IC=-150mA, IB=-15mA	-	-	-0.4	V
		IC=-500mA, IB=-50mA	-	-	-1.6	V
Base-emitter saturation voltage	VBE(sat)	IC=-150mA, IB=-15mA	-	-	-1.30	V
		IC=-500mA, IB=-50mA	-	-	-2.60	V
Transition frequency	fT	VCE=-20V, IC=-50mA, f=100MHz	-	200	-	MHz

CLASSIFICATION OF hFE


RANK	L	H
RANGE	100-200	200-300

Typical characteristics





Package Information

Carrier Dimension(mm)




Dimensions are in millimeter

Pkg Type	A0	A1	B0	B1	K0	D0	D1	E	F	P0	P1	P2	10*P0	W	T
SOT-23	3.15	1.09	2.77	2.15	1.22	1.55	1.00	1.75	3.50	4.00	4.00	2.00	40.00	8.00	0.20
(Tolerance)	±0.1	±0.1	±0.1	±0.1	±0.1	±0.1	±0.1	±0.1	±0.1	±0.1	±0.1	±0.1	±0.2	±0.1	±0.03



Reel Dimension(mm)




Reel Option	D	D1	D2	G	H	I	W1	W2
7" Dia	Φ178.00	54.40	13.00	R78.00	R25.60	R6.50	9.50	12.30
Tolerance	±2	±1	±1	±1	±1	±1	±1	±1

Package Specifications


Package	Reel Size	Reel DIA. (mm)	Q'TY/Reel (Kpcs)	Box Size (mm)	QTY/Box (Kpcs)	Carton Size (mm)	Q'TY/Carton (Kpcs)
SOT23	7'	178	3	210*208*203	45	440*400*230	180

Recommended Soldering Profile for Rectifier Diodes (Pb Free)

a) Wave Soldering Profile



b) Reflow Soldering Profile (Pb Free Application), refer to IPC/JEDEC J-STD-020






Preheat/Soak Temperature Min (T _{smin}) Temperature Max (T _{smax}) Time (ts) from (T _{smin} to T _{smax})	50 °C 200 °C 60-120 seconds
Melting Point of Solder (Sn Ag Cu)	217°C
Ramp-up Rate to 217°C(Melting Point of Solder)	3°C/sec
Time at Temp.>217°C (Melting Point of Solder)	60~150 Sec
Peak Temperature	255±5°C
Time within 5°Cbelow Peak Temp.	20~40 Sec
Cooling Rate	6°C/sec (max)
Time from 25°C to Peak Temp.	8min (max)

c) Manual Soldering

When using an electric soldering iron for manual soldering, it is recommended that the temperature does not exceed 300°C and the soldering time is less than 10 seconds.

Outline Drawing

SOT-23




DIM.	MILLIMETER		
	MIN.	NOM.	MAX.
A	0.90	1.00	1.10
A1	0.00	-	0.10
D	2.80	2.90	3.00
E	2.30	2.40	2.50
E1	1.20	1.30	1.40
L	0.45	0.55	0.65
L1	0.20	-	0.55
b	0.30	0.40	0.50
c	-	0.10	0.15
e	-	1.90	-

Dimensions in inches and (millimeters)

Suggested Soldering Pad Layout

SOT-23



Dimensions in inches and (millimeters)

Important Notice

DongChen Electronics reserves the right to make changes without further notice to any products herein.

DongChen Electronics makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does DongChen Electronics assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages.

“Typical” parameters which may be provided in DongChen Electronics data sheets and/or specifications can and do vary in different applications and actual performance may vary over time.

All operating parameters, including “Typicals,” must be validated for each customer application by the customer’s technical experts.

DongChen Electronics does not convey any license under its patent rights nor the rights of others.

The products listed in this document are designed to be used with ordinary electronic equipment or devices.

Should you intend to use these products with equipment or devices which require an extremely high level of reliability and the malfunction of which would directly endanger human life (such as medical instruments, aerospace machinery, nuclear-reactor controllers, fuel controllers, and other safety devices), please be sure to consult with our sales representative in advance.

Head Office

Contact Information:

DongChen Electronics Co.,Ltd.

Address: 2F., No.407, Sec. 2, Longgang Rd.,Zhongli Dist.,
Taoyuan City 32097, Taiwan (R.O.C.)

Tel: 03-284-1808

Fax: 03-284-1404

Mail:dc@dongchen.com.tw

Web:www.dongchen.com.tw