



REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.03.27	桑葚
A1	N/A		图面升级整理图面	2025.12.26	阿树






3D VIEW

规格 Specifications:
额定电压 Voltage rating:125VAC/DC.
额定电流 Current rating:1A AC/DC
耐电压 Withstanding voltage:500V AC/minute
温度区间 Temperature range:-25°Cto+85°C
绝缘电阻 Insulation resistance:≥100MΩ Min
接触电阻 Contact resistance:≤20mΩ Max

PART NO.:

X1002 W R S-12 B-9T SN
① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- ①Series No
- ②Category:W-Wafer
- ③Welding Board Angle:R-Straight 90°
- ④Welding Way: S-SMT
- ⑤Row No -Pin No:XX-02P-20P
- ⑥Plug the Pin & Special No:B-Ultra-thin With Lock
- ⑦Material:6T-PA6T;9T-PA9T;1T-PA10T;
HT-HTN 6T 94V-0
- ⑧Planting Category:
SN-Bright tin plating 70u'' Min.;30'' Ni Min.
SW-Matte Tin plating 70u'' Min.;30u'' Ni Min.



Poles	Dimensions/mm			Poles	Dimensions/mm		
	A	B	C		A	B	C
02	1.00	3.90	2.50	12	11.00	13.90	12.50
03	2.00	4.90	3.50	13	12.00	14.90	13.50
04	3.00	5.90	4.50	14	13.00	15.90	14.50
05	4.00	6.90	5.50	15	14.00	16.90	15.50
06	5.00	7.90	6.50	16	15.00	17.90	16.50
07	6.00	8.90	7.50	17	16.00	18.90	17.50
08	7.00	9.90	8.50	18	17.00	19.90	18.50
09	8.00	10.90	9.50	19	18.00	20.90	19.50
10	9.00	11.90	10.50	20	19.00	21.90	20.50
11	10.00	12.90	11.50				

X1002WRS-XXBHF-6TSW	PA6T UL 94V-0 (Halogen Free)	Phorphos Bronze	Matte Tin Plating
X1002WRS-XXB-1TSW	PA10T UL 94V-0		
X1002WRS-XXB-HTSW	HTN6T UL 94V-0		
X1002WRS-XXB-9TSW	PA9T UL 94V-0		
X1002WRS-12B-9TSN	PA9T UL 94V-0		
PART NO	Material	Material(Pin And Solder Tabs)	Finish(Pin And Solder Tabs)

RECOMMENDED P.C.BOARD LAYOUT
(TOLERANCE:±0.05)

AuGLAR	±5°
X.x	±0.40
X.xx	±0.30
X.xxx	±0.20
UNSPECIFIED TOLERAUCES	±0.15



DESIGN	阿树	VIEW:	UNIT: mm/in	MODEL TYPE: 1.00mm Crimp Style Connector
CHECKED		UNIT: mm/in		PART NO.: X1002WRS-12B-9TSN
APPROVED		SIZE: A4		DWG NO.: