



This document contains proprietary information and such information may not be disclosed to others for any purposes, not used for sales/marketing/procurement purposes without written permission

REV	DESCRIPTION OF REVISION	ECN NO.	BY	DATE	APPROVED
A	Initial Release	—	H.wei	19/03/17	19/03/17



1 Electrical Data

- 1.1 Impedance: 50Ω
- 1.2 Working voltage: 335V(rms)
- 1.3 Frequency Range: 0-18GHz
- 1.4 Insulation resistance: 5000MΩ min
- 1.5 Dielectric strength: 1000V
- 1.6 Center contact resistance: 3MΩ max
- 1.7 Outer contact resistance: 2.5MΩ max
- 1.8 VSWR: 1.3:1

2 Material&Finish

- 2.1 Inner Contact: gold plated over Beryllium-copper.
- 2.2 Outer Contact: gold plated over brass.
- 2.3 Insulators: Teflon

Notes:

- 1. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE NOTICE AT ANY TIME
- 2. CUSTOMER OUTLINE DRAWING FOR REFERENCE ONLY

DRAWN: H.wei 19/03/17	TITLE: RF Coaxial Connector RF Connector SMA Female PCB Mount	 成都恒利泰科技有限公司 Chengdu HenryTech Technology co., Ltd			
ENGINEER: L.yu 19/03/17					
APPROVED: W.yi 19/03/17		 DIMENSION IN MILLIMETERS (mm)			
TOLERANCES UNLESS OTHERWISE SPECIFIED: X ±0.50 .X ±0.20 .XX ±0.10 ANGLES ±1°	PART NO: HL-SMA-KHDC2	SIZE: A4	SCALE: N/A	SHEET: 1/1	REV: A