



1.00xNo.of Positions+0.40±0.30


1.00xNo.of Contacts-1.00±0.15



2.50 [0.098]



C=2.00 [0.079]



D=2.00±0.25 [0.079]

■ 规格 Specifications:

- 额定电压 Voltage rating:250VAC/DC。
- 额定电流 Current rating:0.75A AC/DC
- 耐电压 Withstanding voltage:300V AC/minute
- 温度区间 Temperature range:-40℃to+105℃
- 绝缘电阻 Insulation resistance:≥500MΩ Min
- 接触电阻 Contact resistance:≤20MΩ Max
- 材料 Material: PA6T UL94V-0
- 镀层 Planting Category: 1U"Gold
- 回流焊温度 Reflow soldering temperature:260±5℃,10s

X3021 F V- 2x07 - C20 D20
① ②③ ④ ⑤ ⑥

- ① Series No.
- ② Category:F-Female
- ③ Welding Board Angle:V-Stright 180°
- ④ Row No -Pin No:2xXX-2x03P-2x50P
- ⑤ Plastic height: C=2.0mm
- ⑥ Plastic length:D=2.0mm

Ø0.60 [Ø0.024]

1.00 [0.039]



P.C.B LAYOUT

X3021FV-2x07-C20D20	PA6T UL94V-0	Phosphor Bronze	1U"Gold	X3021W
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB Wafer

					ANGLAR	±5°
Δx					L≤ 4	±0.2
Δx					4<L≤ 16	±0.3
Δx					16<L≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L> 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

XKLB

XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND		SCALE: N/A	MODEL TYPE: 1.00mm Crimp Style Connector		
DWN		VIEW: 	PART NO.: X3021FV-2x07-C20D20		
CHKD		UNIT: mm/in	DWG NO.: X-X3021FV-2x07-C20D20		
APPD		SIZE: A4			
PRECISION CO.,LIMITED			WEIGHT	SHEET	REVISION
				1/1	A0