



	REVISIONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		新增卡扣R角, 增强卡扣强度	2024.03.14	桑 葦



ANGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERANCES	



3D VIEW

Specifications (规格):

1. Voltage rating(额定电压):250V AC DC
2. Current rating(额定电流):5.0A AC/DC
3. Withstanding voltage(耐压值): $\geq 1500\text{V AC/minute}$
4. Insulation resistance(绝缘电阻): $1000\text{M}\Omega \text{ Min}$
5. Contact resistance(接触电阻): $20\text{m}\Omega \text{ Max}$
6. Temperature range(使用温度):- $25^{\circ}\text{C} \sim +85^{\circ}\text{C}$

PART NO.:

$\frac{X3025}{\textcircled{1}}$
 $\frac{H}{\textcircled{2}}$
 $\frac{M}{\textcircled{3}}$
 $\frac{M-2 \times 07}{\textcircled{4}}$
 $\frac{N2}{\textcircled{5}}$

- ① Series No
② Category:H-Housing
③ Welding Board Angle:M-Male Housing
④ Row No-Pin: 2x01-2x12P
⑤ Material:N2-PA66, UL 94V-2, BLACK

X3025HM-2x07-N2	PA66 94V-2	BLACK	X3025W	X3025TF
PART NO.	MATERIAL	COLOR	Suitable XKB Wafer	Suitable XKB Terminal

DESIGN	桑 菴	VIEW: 	MODEL TYPE: 3.0mm Crimp Style Housing		
CHECKED		UNIT: mm/in	PART NO.: X3025HM-2x07-N2		
APPROVED		SIZE: A4	DWG NO.: X-X3025HM-2x07-N2		
PRECISION CO.,LIMITED			SCALE N/A	PAGE 1 / 1	REVISION A0