




Scrolls (S)




1:With 2:Without



RECOMMENDED PCB LAYOUT(TOP VIEW)

GENERAL TOLERANCES:±0.05



Flat(F)

Material

Housing Material: LCP, UL94V-0, black

Contact Terminal: Copper Alloy

Metallic Shell: Sus

Electrical

Voltage Rating: 30 V AC

Current Rating: Signal (Pins 2,3,4): 1.0A, Power (Pins 1,5): 1.8A

Contact Resistance: 30mΩ Max

Insulation resistance: 1000MΩ Min

Dielectric withstanding voltage: 250V AC/Minute

Mechanical

Durability: 10,000 cycles

Mating Force: 35N (3.57Kgf) Max

Unmating Force: 8N (0.82Kgf) Min.

U254-051T-4BHJ25-S2S

1:Au 1U*
6:Au 30U*
T:TIN
N:NICKEL

S:Sus
2:Without
S:Scrolls F:Flat

							DSND		DATE		SCALE: N/A	MODEL TYPE: MICRO USB		
ΔX					ANGLAR	±5°	DWN		DATE		VIEW: 	PART NO.: U254-051T-4BHJ25-S2S		
ΔX					4<L≤16	±0.3	CHKD		DATE		UNIT: mm	DWG NO.: X-U254-051T-4BHJ25-S2S		
ΔX					16<L≤63	±0.4	APPD		DATE		SIZE: A4			
MARK	DESCRIPTION			DATE	REVISED	APPROVED						L>63	±0.5	
REVISIONS							UNSPECIFIED TOLERANCES					XKB INDUSTRIAL PRECISION CO.,LIMITED		
www.xk-dg.cn www.1k0k.com www.1k0k.cn														
												WEIGHT	SHEET	REVISION
												1.0g	1/1	A0