




HSF



ROHS



A2



SPECIFICATION

Current Rating:	1.5 Amp
Insulation Resistance:	1000M ohms min
Contact Resistance:	20M ohms max
Dielectric Withstanding:	AC500V
Operating Temperature:	-65°C to +125°C
Contact Material:	Brass
Insulator Material:	PA6T,UL 94V-0 Black

Ordering Code:

PHDR05 - X - X - D - A-B - X - X

①	②	③	④	⑤	⑥	⑦
---	---	---	---	---	---	---

① Series No:

② No. of Contacts

02 To 80

③ Contact Plating:

G0:Gold flash S0:Selective

G1:3U" Gold S1:Selective 3u"

G2:5u" Gold S2:Selective 5u"

G3:10u" Gold S3:Selective 10u"

G4:15u" Gold S4:Selective 15u"

G5:30u" Gold S5:Selective 30u"

SN:Tin

④ Connector Type

D: Dual

⑤ Pin Length:

A:0390=3.90mm

B:0300=3.00mm

Please mark the desired length in the A/B

⑥ Insulator Material

A:PBT

B:PA6T

C:LCP

D:PA46

E:PA9T

⑦ Packing:

A:Tray


B:Bag

T:Tube

U:Tube+CAP

R:Tape&Reel

W:Tape&Reel+CAP



PCB LAYOUT

客户料号:


17415000001314

Standard IE P/N:

PHDR05-18G0D03900300BB

A	B	Unless Otherwise specified tolerance	
3.9	3.0	X. ±0.35	X.XX: ±0.20
		X.X: ±0.25	X.XXX: ±0.15
Optional		SCALE: As Shown	UNIT: mm

DRAW YG ZHONG	DATE 03/22/2016
CHECK BobYang	DATE 03/22/2016

ANTENK ELECTRONICS CO.,LTD
Http://www.antenk.com
E-mail:sales@antenk.comTITLE:
2.00mm Pin Header DualRow Angle Type H:4.0

DRAWING NO: PHDR05-18G0D03900300BB

PRODUCT NO: PHDR05-18G0D03900300BB

A2

Revise Insulation dimension based on sample

2023/05/24

A1

Increase packing method and material

2016/10/25

REV

DESCRIPTION

DATE