

Johanson Part Number VBEF302W103K1GV001E

Johanson Part Number: VBEF302W103K1GV001E

Johanson Company: JDI

Legacy P/N: 302S47W103KV4E-BME

Size for Capacitors (EIA): 2220

Description: Capacitors HVS BME, 2220, X7R,
3000V, 0.01 μ F $\pm$ 10%, Ni/Sn (RoHS), 7" Reel
Embossed Tape

Specification Number: None

Life Cycle Stage: Active

NCNR: No

AEC Q200 Qualified: No

Thickness (Max): 0.150

Schedule B: 8532.24.00.20

Thickness (Min): None

ITAR: No

End Band(Min): 0.01

ECCN: EAR99

End Band (max): 0.040

RoHS Compliance: Yes, RoHS 10/10

Standard Item: Yes

REACH: Yes

Lead Time Typical (Weeks)*: 16

Country of Origin: US, MX, TW, or CN

Length (Min): 0.210

Product Family: Capacitors

Length (Max): 0.240

Product Subfamily: Capacitors High Voltage SMD $\geq$
500V

Width (Min):0.185

Capacitance Value: 0.010

Width (Max): 0.215

Cap Unit of Meas: μ F

Part Weight (mg): None

Tolerance: $\pm$ 10%

Packaged Width (lb) Arm: None

Voltage: 3000.0

Packaging: 7" Reel Embossed Tape

Dielectric Temp Coefficient: X7R

Packaging Qty: None

Termination: 68

Operating Temp Range: -55°C to +125°C

Marking: No Mark

Storage Temp Range (Packaged): +5°C to +40°C
with RH 20% to 70%

Product Release Date: Jan. 3, 2006

Storage Temp Range (None Operating): -65°C to
+125°C

Harmonization: 8532.24.00.20

*This can vary significantly so it is important to obtain a quotation with lead time for production planning purposes.

Web Page Link: <https://www.johansondielectrics.com/high-voltage-mlc-capacitors>

Printed from: <https://www.johansontechnology.com/part/VBEF302W103K1GV001E/>