



Recommended PCB Layout
Total tolerance:±0.05mm

X3025WV-10 -66SN	PA66 UL 94V-0	Brass	Tin-Plated	X3025H
X3025WV-10- 46SNP	A46 UL 94V-0			
X3025WV-10-N0SNP	A9T UL 94V-0			
PART NO	Material	Material(Pin)	Finish(Pin)	Mate s With XKB Housing

Poles	Dimensions(mm)		
	A	B	C
02	3.00	9.65	9.00
03	6.00	12.65	12.00
04	9.00	15.65	15.00
05	12.00	18.65	18.00
06	15.00	21.65	21.00
07	18.00	24.65	24.00
08	21.00	27.65	27.00
09	24.00	30.65	30.00
10	27.00	33.65	33.00
11	30.00	36.65	36.00
12	33.00	39.65	39.00

X3025 W V -10 - N0 SN

①	②	③	④	⑤	⑥	⑦	⑧	⑨
---	---	---	---	---	---	---	---	---

① Series No.

② Category : W-wafer

③ Welding Board Angle: V- Straight 180°

④ Welding Way: Blank-DIP

⑤ Row No.-Pin No.: XX-02P~12P

⑥ Plug the Pin & Special No.:

⑦ Material: 46-PA46 94V- N0-PA9T 94V-0;
XKB 66-PA66 94V-0

⑧ Planting Category: SN-Bright tin plating

⑨ Color: Blank-Natural Color

■ Specifications :

- Voltage rating: 250V AC / DC
- Current rating: 5A AC / DC
- Withstanding voltage: 1500V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: $\geq 1000M\Omega$
- Contact resistance: $\leq 10m\Omega$ XKB
- After environmental testing : $\leq 20m\Omega$

				XKB	ANGLAR	±5°	DWN		DATE		VIEW: 	3.00mm Crimp Style Connectors	
Δx					L ≤ 4	±0.2	CHKD		DATE		UNIT: mm/in	PART NO.: X3025WV-10-N0SN	
Δx					4<L ≤ 16	±0.3						DWG NO.: X-X3025WV-10-N0SN	
Δx					16<L ≤ 63	±0.4							
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L > 63	±0.5	APPD		DATE		SIZE: A4		
REVISIONS							UNSPECIFIED TOLERANCES			XKB INDUSTRIAL PRECISION CO.,LIMITED			WEIGHT 1.0g
www.helloxkb.com													SHEET 1/1
													REVISION A0