

REV.		ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0		N/A		INITIAL RELEASE	/	/
A1		N/A			2025.10.14	

Technical Data

Material


Contact Material: Brass/Phosphor Bronze
Contact plating: Nicker/Gold Flash
Insulator Material: Black Polyester UL94V-0
Standard: PBT+30%G F

Electrical

Current rating: 3.0Amps/contact max
Contact resistance: $\leq 20\text{m}\Omega$ / contact
Insulation resistance: $\geq 1000\text{MQ}$ at V=100V
Withstanding Voltage: 1000V AC/minute

Mechanical

Operating temperature: -40 C to +105C



X2540-B 1 GN B

HOUSING COLOR:
B:BLACK BL:BLUE
Y:YELLOW W:WHITE
GR:GREEN R:RED
CONTACT PLATING:
GF:FULL GOLD FLASH
NI:NICKEL
GN:GOLD+NICKEL

HEIGHT:
0:6mm
1:6.5mm

HOUSING TYPE:
A:OPEN
B:CLOSE
C:LONG

AuGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERANCES	



DESIGN		VIEW:	MODEL TYPE: 2.54 CONN
CHECKED		UNIT: mm/in	PART NO.: X2540-B1GNB
APPROVED		SIZE: A4	DWG NO.:
SCALE			PAGE
N/A			1/1
REVISION			A1