





REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.09.30	阿树



Specifications:
规格:
Voltage rating:400V AC/DC
额定电压: 400V AC/DC
Current rating:0.75A AC/DC
额定电流: 0.75A AC/DC
Withstanding voltage:1800V AC/minute
耐受电压: 1800V AC/分钟
Temperature range:-40℃-+125℃
温度范围: -40℃-+125℃
Insulation resistance:1000MΩ min
绝缘电阻: 1000MΩ Min
Contact resistance:30mΩ Max
接触电阻: 30mΩ Max



PART NO.:

X5015 W R S-02 A-LP SW
① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- ①Series No
- ②Category:W-Wafer
- ③Welding Board Angle:R-Stright 90°
- ④Welding Way: S-SMT
- ⑤Row No.Pin No:XX-02 Pin
- ⑥Special No:A-Posterior sulcus
- ⑦Material:LP-LCP UL94V-0
- ⑧Plating:SW-Matte Tin Plated

P .C .B Layout

X5015WRS-02A-LPSW	LCP	Brass	X5015H-A
PART NO	Material	Material(Pin)	Suitable XKB Housing

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:		MODEL TYPE:	5.0mm Crimp Style Connector
CHECKED		UNIT:	mm/in	PART NO.:	X5015WRS-02A-LPSW
APPROVED		SIZE:	A4	DWG NO.:	X-X5015WRS-02A-LPSW