








Specifications :

- Voltage rating: 50 V AC / DC
- Current rating: 1A AC / DC
- Withstanding voltage: 500V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: ≥100MΩ
- Contact resistance: ≤20mΩ
- After environmental testing:≤40mΩ

X1002 W R S- 14-E-LP SW HF
① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

- ① Series No.
- ② Category : W-WAFER
- ③ Wedding Board Angle : V-Stright Angle 180°
- ④ Welding Way:S-SMT
- ⑤ Row No.Pin No.XX-02P~20P
- ⑥ Plug the Pin & Special No:E-Ear clip
- ⑦ Material:LP-LCP 94V-0
- ⑧ Planting Category: SW-Matte Tin plating(Tin:70u Min)
SN-Bright tin Plating
V01-Gold Flash
- ⑨ HF-Halogen Free;Blank-Halogen

Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C
02	1.00	4.00	2.50	11	10.00	13.00	11.00
03	2.00	5.00	3.50	12	11.00	14.00	12.00
04	3.00	6.00	4.50	13	12.00	15.00	13.00
05	4.00	7.00	5.50	14	13.00	16.00	14.00
06	5.00	8.00	6.50	15	14.00	17.00	15.00
07	6.00	9.00	7.50	16	15.00	18.00	16.00
08	7.00	10.00	8.50	18	17.00	20.00	18.00
09	8.00	11.00	9.50	20	19.00	22.00	20.00
10	9.00	12.00	10.50				

X1002WRS-14E-LPSWHF	LCP UL 94V-0	Brass	Tin Plated	X1002H-L
X1002WRS-14E-LPV01	LCP UL 94V-0	Phosphor Bronze	Gold Flash	X1002H
X1002WRS-14E-LPSW	LCP UL 94V-0		Tin Plating Fog	
PART NO	Material	Material(Pin And Solder Tabs)	Finish(Pin And Solder Tabs)	Suitable XKB Terminal

							DSND		DATE		SCALE: N/A	MODEL TYPE: 1.0mm Crimp Style Connectors				
Δx						ANGLAR		DWN		DATE		VIEW: 	PART NO.: X1002WRS-14E-LPSWHF			
Δx						$L \leq 4$	±0.2									
Δx						$4 < L \leq 16$	±0.3	CHKD		DATE		UNIT: mm/in	DWG NO.: X-X1002WRS-14E-LPSWHF			
Δx						$16 < L \leq 63$	±0.4									
MARK	DESCRIPTION			DATE	REVISED	APPROVED	$L > 63$	±0.5	APPD		DATE		SIZE: A4	X-X1002WRS-14E-LPSWHF		
REVISIONS							UNSPECIFIED TOLERANCES		XKB INDUSTRIAL PRECISION CO.,LIMITED					WEIGHT	SHEET	REVISION
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn														1.0g	1/1	A0