



深圳市咸阳华星机电有限公司
SHENZHEN XIANYANG HUAXING MACHINERG & ELECTRONIC.CO;LTD

产品规格书 (APPROVAL SHEET)

客户名称 Client				
品 名 Description	线绕型晶圆电阻器（双帽）			
规 格 Specification	RXM 0207J --0309J--0410J--0411J 系列承认			
料 号 Part No				
生产方	工艺审核 TECHNICAL	品质审核 QUALITY	项目审核 PROJECT	开发审核 DEVELOPING
客户方	工艺审核 TECHNICAL	品质审核 QUALITY	项目审核 PROJECT	开发审核 DEVELOPING



深圳市咸阳华星机电有限公司
SHENZHEN XIANYANG HUAXING MACHINERG & ELECTRONIC.CO;LTD



佛山市华欣电子有限公司

Foshan Huaxin Electronics Co., Ltd

电话 TEL: 0755—81785561 0757-27783601

传真 FAX: 0757-27783601

网址 Http://www.szxyhx.com

邮箱 Email: szxyhx@163.com

地址 Add:

深圳市宝安区燕罗街道燕川社区红湖路 168 号厂房 1 栋第四层

广东省佛山市顺德区杏坛镇高赞村二环路 8 号顺德智富园 36 栋 601



深圳市咸阳华星机电有限公司

SHENZHEN XIANYANG HUAXING MACHINERY & ELECTRONIC CO., LTD

1. 适用范围 Applicable Scope


此基准是供应充电器、节能灯、电源供应器等用之不燃性涂装型绕线电阻器之规格。

Applicable Scope: This benchmark is the supply of chargers, power supply, and other energy-saving lamps used in the coating are incombustibility wound resistor type of specifications.

2. 形名 Part Number

依据其种类、额定电力、端子形状、公称电阻值及容许误差等分别注明。

It is composed by Type, Rated Wattage, Terminal Form, and Nominal Resistance and Tolerance. e.g.



2-1. 种类 Type

绕线型晶圆电阻器以 RXM 表示之。

Wire Wound ME is called "RXM"

2-2. 额定电力 Rated Wattage

额定电力(W)以数字表示, 如 1WS。

Shown by "W", such as 1WS.

2-3. 标称电阻值 Nominal Resistance Value:

Ω 为单位, 依据 JIS-C6402 为适用原则(E-24 Series)。

Ω are its unit which is in accordance with JIS-C6402(E-24)series.

2-4. 电阻值及容许误差 Tolerance

在室温中依检测器测量, 应在指定电阻值之容许误差以内。

It is measured by Bridge-method at room temperature and expressed by a capital letter.

F $\pm 1\%$ G $\pm 2\%$ J $\pm 5\%$

2-5. 镍铬或康铜等合金线 Nickel Chrome or nickel an copper alloy.



深圳市咸阳华星机电有限公司

SHENZHEN XIANYANG HUAXING MACHINERG & ELECTRONIC.CO;LTD

3. 额定电力 Rated power

额定电力是周围温度 70℃ 以下可连续使用之负载电力最大值数,且应使机械性能与电气性能满足。又周围温度超越上记温度时,依照图一之电力轻减曲线而定。

Rated power is the value of Max load voltage specified at the ambient temperature of 70℃ and shall meet the functions of electrical and mechanical performance. When the ambient temp.surpasses above Mentioned temperature. The value declines as following DERATING CURVE:




图 1: 负载减轻曲线

3-1. 额定电压 Rated Voltage

依公式 $E = \sqrt{RP}$ 求出连续使用额定电压,如额定电压超出最高使用电压,则以最高使用电压为连续使用额定电压

It is calculated as the following formula $E = \sqrt{RP}$

However, in case the voltage calculated exceeds the maximum load voltage, such the maximum load. Voltage shall be regarded as its rated voltage, means whichever less.

E=连续使用额定电压 E=Rated Continuous Working Voltage(V)


P=额定功率 P=Rated Power(W)

R=公称电阻值 R=Nominal Resistance Value(Ω)

3-2 备注

RXM 阻抗范围 1Ω-100Ω


4. 构造 CONSTRUCTOION



1. 端子 (TERMINAL)
2. 标示 (NONFLAME PAINT WITH SOL VENT-PROOF)
3. 绝缘涂层 (INSULATION COATING)
4. 基体 (MATRIX)
5. 绕线 (WIRE WRAPPING)



5. 规格及尺寸 SPECIFICATIONS



TYPE	DIMENSION(mm)					
	L	D Max	D1 Max	D2 Max	S	C
0207	6.1±0.3	2.5	2.15	2.6	0.2±0.05	1.2±0.1
0309	8.9±0.3	3.4	2.95	3.45	0.2±0.05	1.6±0.1
0410	10±0.5	3.8	3.5	4.0	0.25±0.05	1.85±0.1
0411	11±0.5	4.6	4.05	4.7	0.25±0.05	1.85±0.1

备注： L 为双帽总长度，D 为涂漆的厚度，D1 为内帽总高度，D2 为外帽总高度，S 为铁帽的厚度，C 为外帽的宽度。

6. 机械性能 Mechanical Performance


6-1. 端子拉力强度 Terminal Tensile

将电阻本体一端固定,另一端向电阻体轴方向,慢慢加重至 2.5Kg 后,保持 10 秒钟,本体不得脱落或松动。

Fixing the resistor body, a static load of 2.5Kg is to be gradually applied into the terminal for 10seconds without causing any looseness and fall.

7. 使用温度: Operating Temperature Range

-55℃～275℃ 以内



深圳市咸阳华星机电有限公司

SHENZHEN XIANYANG HUAXING MACHINERG & ELECTRONIC.CO;LTD

8.电气特性 ELECTRICAL PERFORMANCE


项目 ITEM	规格值 SPECIFICATIONS	试验方法 TEST METHODS (JIS C5202)
抵抗值 DC Resistance	须在规定之 R 值的容许差内 Allowed under R rate tolerance	 HM-9350
绝缘耐压 Dielectric Strength Test	涂装不可损坏, 绝缘不可破坏 No evidence of flashover or mechanical damage action insulation breakdown	电阻体置于 V 型槽上, 使用 300V 电压加压 60 秒 Resistance body placed in the v-groove, use 300 V voltage pressure 60 seconds
可焊性 Solder ability	端子表面积 95%以新焊锡所覆盖为原则 95% Surface of terminal covered solder	浸入 270℃ ±10℃的锡炉, 5 秒 Into the tin stove 270 °C ± 10 °C, 5s
耐焊接热 Resistance to soldering Heat	±(1%+0.05Ω)以内 within ±(1%+0.05Ω)	浸入 260℃ ±5℃的锡炉, 5~10 秒 Into the tin stove 260 °C ± 5 °C, 5~10s
短时间过负载 Short time over load	±(2%+0.05Ω)以内 ±(2%+0.05Ω) Less than	额定功率 2.5 倍测试 5 秒 2.5Times rated voltage for 5s
负载寿命 Load Life	±(5%+0.05Ω)以内 Within ±(5%+0.05Ω)	70℃1000 小时 额定电压(90 分钟 ON,30 分钟 OFF) 70℃1000h Rated voltage
耐溶剂性 Resistance to solvent	涂漆及色码无脱落 No deterioration of protective coating and markings	放入稀释剂中 3 分钟 Add thinner in 3min
不燃性 Incombustibility	无出现火焰 No evidence of flame	UL1412 标准 UL1412 standard
熔断特性 Fusing character tic	60 秒内熔断 Fusing time is within 60s	恒流 2.20A, 熔断电流 = $\sqrt{R \times P \times 16 / R}$ Rated power x 16



深圳市咸阳华星机电有限公司

SHENZHEN XIANYANG HUAXING MACHINERG & ELECTRONIC.CO;LTD

9.色码表示 Color Coding



Color 颜色	第一条 1 the significant	第二条 2 nd significant	倍数 Multiplier	误差 Error
Black 黑	0	0	10^0	
Brown 棕	1	1	10^1	$\pm 1\%(F)$
Red 红	2	2	10^2	$\pm 2\%(G)$
Orange 橙	3	3	10^3	
Yellow 黄	4	4	10^4	
Green 绿	5	5	10^5	
Blue 蓝	6	6	10^6	
Violet 紫	7	7		
Grey 灰	8	8		
White 白	9	9	10^{-3}	
Golden 金			10^{-1}	$\pm 5\%(J)$
Silver 银			10^{-2}	$\pm 10\%(K)$

注:Note 本体面漆: 涂灰色不燃性绝缘漆。 Body coating Grey

10. 注意事项 REQUIREMENTS IN USE

- 湿气会使电极之焊锡劣质化,保持场所在温度 40°C 以下,湿度 70% 以下。
IN THE HIGH HUMIDITY SITUATION, IT WILL MAKE THE SOLDER ABILITY WORST. PLEASE PRESERVE THE RESISTORS IN 40°C ,70 RH BELOW
- 尽量不要打开最小包装。
PLEASE DON'T OPEN THE MINE PACKAGE WHEN YOU PRESERVE IT
- 周围温度高时按照负荷减轻曲线图减少规定使用电力。
WHEN IN THE HIGH TEMPERATURE SITUATION, PLEASE ACCORD TO THE PICTURE OF "POWER DERATING CURVE" REDUCE THE USE OF POWER RATING
- 尽量不要将多个电阻并列或直列连结, 而以大电压或大电流使用。
YOU SHOULD AVOID THE CONNECTOR OF RESISATNCE REPLACED BY LATGE VOLTAGE AND POWER
- 由于不燃性涂料承受外部冲击力较弱, 故在各种处置中应减少对电阻体的碰撞。
AS THE PAINT IS NOT SUBJECT TO EXTERNAL SHOCKS INCOMBUSTIBILITY LESS,



深圳市咸阳华星机电有限公司

SHENZHEN XIANYANG HUAXING MACHINERG & ELECTRONIC.CO;LTD

IT SHOULD BE DISPOSED OF IN A VARIETY OF REDUCING THE BODY'S RESISTANCE COLLISION

6. 清洗后，外涂绝缘漆多少会弱化，然后自然放置后可复元其强度,所以洗净后 20 分钟内不要让电阻皮膜与任何品之接触。


AFTER CLEANING THE BODY, IT WILL MAKE THE FILM WEAKER. BUT IF YOU LET IT NATURE DRY WITHOUT TOUCHING OR PAINTING

ANYTHING, THE RESISTORS WILL RECOVER ITS STRENGTH BY 20 MINUTES

7. 电阻为发热性零件，所以在使用中电阻间不应相互排列过密或接近其他发热零件,而妨碍其散热性，必要时应增加散热装置。


THE RESISTORS ARE REQUESTED NOT TO PLACE BY THE OTHER HEATING ACCESSORIE, WHICH WILL OBSTRUCT THEIR HEAT DISSIPATION, NECESSARY TO INCREASE COOLING DEVICE

11. 包装卷轴规格尺寸 Packaging reel sizes



Unit:mm


Type	ΦA	ΦB	ΦC	W	T	Bmboss Plastic Tape(EA)
0207	178.5±1.5	60.0+1.0	13.0±0.5	13.0 + 0.5	15.5±0.5	2,000(7.0") 6, 500(13")
0309	330±1.5	100.0+1.0	13.0±0.5	17.0±0.5	19.0±0.5	2,500(13")
0410	330±1.5	100.0+1.0	13.0±0.5	25.0±0.3	27.0±0.5	2,000(13")
0411	330±1.5	100.0+1.0	13.0±0.5	25.0±0.3	27.0±0.5	1,500(13")



深圳市咸阳华星机电有限公司

SHENZHEN XIANYANG HUAXING MACHINERG & ELECTRONIC.CO;LTD

12. 载带规格尺寸 With the sizes



Tape	A	B	W	E	F	P0	P1	P2	$\Phi D0$	T
0207	2.6 ± 0.10	6.40 ± 0.1	12.0 ± 0.1	1.75 ± 0.1	5.50 ± 0.05	4.00 ± 0.10	4.00 ± 0.10	2.00 ± 0.05	$1.50+0.10$	2.60 ± 0.10
0309	3.40 ± 0.20	9.10 ± 0.10	16.0 ± 0.30	1.75 ± 0.10	7.5 ± 0.10	4.00 ± 0.10	8.00 ± 0.10	2.00 ± 0.05	$1.50+0.10$	3.40 ± 0.20
0410	4.30 ± 0.10	11.00 ± 0.10	24.0 ± 0.30	1.75 ± 0.10	10.0 ± 0.10	4.00 ± 0.10	8.00 ± 0.10	2.00 ± 0.05	$1.50+0.10$	4.30 ± 0.10
0411	4.80 ± 0.10	12.20 ± 0.10	24.0 ± 0.30	1.75 ± 0.10	11.5 ± 0.10	4.00 ± 0.10	8.00 ± 0.10	2.00 ± 0.10	$1.50+0.10$	4.80 ± 0.10

13. 版本变更记录 (Version change records)



深圳市咸阳华星机电有限公司

SHENZHEN XIANYANG HUAXING MACHINERY & ELECTRONIC CO., LTD

日期 Date	料号 P/N.	规格 P/N	变更 内容 Changes	变更前 Before the change	变更后 After the change
2021-09-08		RXM 0207J--0309J--0410J--0411J	初次发行		