

ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE





一、MATERIAL:

- 1.Insulator:PBT+30%Glass Fiber
- 2.Contact:Brass
- 3.Contact Plated:Gold Flash over Tin Or Glod Plated Or Tin Plated
- 4.Shell:Steel,Nickel Plated

二、SPECIFICATION:

- 1.Current Rating:3 AMPS
- 2.Insulation Resistance: 100M Ω MIN. At 500VDC
- 3.Dielectric Strength: 500V for One minute
- 4.Operation Temperature: -55° C~+105° C.

※【胶芯颜色、防火要求、环保要求及电镀规格 依据客户实际订单要求为准】



RECOMMEND PCB LAYOUT (T=1.6)
PCB TOLERANCE:±0.05

COSTOMER DRAWING			LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO., LTD		
DRAWING					
CHECK					
APPROVAL					
TOLERANCES ARE			TITLE	D-SUB连接器15PIN公针弯插	REV. A
30-150	±0.35	ANGLE ±3°	PART NO.	LAIL-D-SUB15P-01-B-W	UNITS mm
10-30	±0.2				
5-10	±0.15				
0-5	±0.1				
			DWG.NO.		Projection 