




HSF



PCB LAYOUT

SPECIFICATION

Current Rating:	3Amp
Insulation Resistance:	1000M ohms min
Contact Resistance:	20M ohms max
Dielectric Withstanding:	AC500V
Operating Temperature:	-65°C to +125°C
Contact Material:	Brass
Insulator Material:	PBT,UL 94V-0 Black

Ordering Code:

PHES04 - X - X - D - A - B - X - X - X
① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- | | |
|---|---|
| ① Series No: | ⑥ Insulator Material |
| ② No. of Contacts
02 To 80 | A: PBT |
| ③ Contact Plating:
G0: Gold flash S0: Selective
G1: 3u" Gold S1: Selective 3u"
G2: 5u" Gold S2: Selective 5u"
G3: 10u" Gold S3: Selective 10u"
G4: 15u" Gold S4: Selective 15u"
G5: 30u" Gold S5: Selective 30u"
SN: Tin | ⑦ Packing:
A: Tray
B: Bag
T: Tube
U: Tube+CAP
R: Tape&Reel
W: Tape&Reel+CAP |
| ④ Connector Type
D: Dual | ⑧ Plastic High
H1: 1.7mm
H2: 2.54mm
H3: 2.00mm
H4: 1.50mm |
| ⑤ Pin Length:
A: 0600=6.00mm
B: 0300=3.00mm
Please mark the desired length in the A/B | |

Standard IE P/N :

PHES04-14-G0-D-0850-0160-E-W-H2

A	B
6.00	3.00

Unless Otherwise specified tolerance

X. ±0.35 X.XX: ±0.20
X.X: ±0.25 X.XXX: ±0.15

Optional

SCALE: As Shown UNIT: mm

DRAW
YG ZHONGDATE
01/05/2016CHECK
BobYangDATE
01/05/2016

ANTENK ELECTRONICS CO., LTD
Http://www.antenk.com
E-mail: sales@antenk.com

TITLE:

2.54mm Pin Header DualRow Straight Type


DRAWING NO: PHES04-14-G0-D-0850-0160-E-W-H2

PRODUCT NO: PHES04-14-G0-D-0850-0160-E-W-H2

REV

DESCRIPTION

DATE



ADD H4=1.5MM

Increase packing method and material

2017/04/14

2016/10/25