

MBR10100LCT/FCT/DC/CS


SCHOTTKY BARRIER RECTIFIER




TO-220AB/CT




TO-220F/FCT



TO-263/DC



TO-252/CS



FEATURES

- Low forward voltage
- High current capability
- High forward surge capability
- Low power losses，High efficiency
- Guarding for over voltage protection

APPLICATIONS

Low VF Schottky barrier rectifier are designed for high freqency, miniature switched mode power supplies such as adapters ,lighting and on-board DC/DC conerters

Primary Characteristic

I_O	2*5A
V_{RRM}	100V
I_{FSM}	150A
V_F	0.64V
$T_J$max	150℃

MECHANICAL DATA

- **Case:** Molded plastic
- **Polarity:** As marked
- **Mounting Position:** Any
- **Molded Plastic:** UL Flammability Classification Rating 94V-0
- Lead free in compliance with EU RoHS 2011/65/EU directive
- Solder bath temperature 275℃ maximum,10s per JESD 22-B106

Maximum Ratings (Per Leg) at Ta=25°C unless otherwise specified

Characteristics		Symbol	Value	Unit
Maximum Repetitive Peak Reverse Voltage		V_{RRM}	100	V
Working Peak Reverse Voltage		V_{RWM}	120	V
Maximum DC Blocking Voltage		V_{DC}	100	V
Maximum Average Forward Rectified Current	Per Leg	I_O	5	A
	Total		10	
Peak Forward Surge Current,8.3 ms Single Half Sine-wave		I_{FSM}	150	A
Operating Temperature Range		T_J	150	°C
Storage Temperature Range		T_{STG}	-40 to +150	°C
Typical Thermal Resistance (Note1) TO-220AB,TO-263,TO-252 TO-220F		$R_{\theta JC}$	 2 4	°C/W

Note1: Thermal resistance from Junction to case per leg mounted on heatsink.

Electrical Characteristics (Per Leg) unless otherwise specified

Characteristics		Symbol	Value		Unit
Forward Voltage Drop(Note2)		V_F	Typ.	Max.	V
at I_F=2A	TA=25°C		0.50	-	
	TA=125°C		0.45	-	
at I_F=3A	TA=25°C		0.56	-	
	TA=125°C		0.52	-	
at I_F=5A	TA=25°C		0.67	0.75	
	TA=125°C		0.64	-	
Maximum Reverse Current at V_R=150V	TA=25°C	I_R	7	30	μA
	TA=125°C		2.0	-	mA

Note2:Pulse test: 300 μs pulse width, 1 % duty cycle

RATINGS AND CHARACTERISTIC CURVES

Fig.1 TYPICAL FORWARD CURRENT DERATING CURVE




Fig.2 Typical Reverse Characteristics




Fig.3 Typical Forward Characteristic






Fig.5 Maximum Non-Repetitive Peak Forward Surage Current




Package Outline Dimensions millimeters

TO-220F




Dim.	Min.	Max.
A	9.95	10.25
B	2.95	3.25
C	1.25	1.45
D	12.80	13.20
E	0.40	0.60
F	2.8	3.5
G	1.30	1.45
H	Typ 2.54	
I	Typ 5.08	
J	4.60	4.75
K	2.45	2. 65
L	6.5	6.8
M	15.4	16.0
N	2.75	3.05
O	0.45	0.55
P	0.70	0.90
All Dimensions in millimeter		

TO-220AB




Dim.	Min.	Max.
A	10.15	10.35
B	2.50	2.95
C	3.70	3.90
D	28.5	29.5
E	1.20	1.40
F	6.20	6.55
G	2.4	2.6
H	15.0	16.0
I	0.35	0.42
J	4.3	4.55
K	1.25	1.35
L	Typ5.08	
L1	13	14
L2	8.5	9.5
M	Typ2.54	
N	2.8	3.5
O	0.70	0.90
All Dimensions in millimeter		

TO-263



Dim.	Min.	Max.
A	10.15	10.35
B	6	8
C	1.2	1.5
D	0.55	1.0
E	5.0	6.0
F	1.4	1.6
G	0.75	0.85
H	1.2	1.5
I	Typ2.54	
J	8.5	9.5
K	4.3	4.55
L	1.25	1.35
M	0.02	0.23
N	2.2	2.8
O	0.30	0.40
All Dimensions in millimeter		

TO-252



Dim.	Min.	Max.
A	2.1	2.5
B	0.95	1.55
C	0.4	0.6
D	6.4	6.7
D1	5.1	5.8
E	5.8	6.4
E1	Typ2.3	
E2	Typ4.6	
B1	0.6	0.8
B2	0.75	0.95
O	--	0.15
L1	9.0	11.0
L2	1.3	1.7
L3	0.70	0.95
All Dimensions in millimeter		