








ROHS



NANO SIM CARD	
Pin No.	NAME
C1	VCC OF SIM
C2	RST OF SIM
C3	CLK OF SIM
C5	GND OF SIM
C6	VPP OF SIM
C7	I/O OF SIM
C4/C8	N/A



RECOMMENDED PCB LAYOUT
GENERAL TOLERANCE ± 0.05



STEP 1 INSERT NANO SIM CARD



STEP 2 PUSH THE SHELL



STEP 3 FINISH

NOTES:

1.MATERIAL:


- 1.1 Housing:High Temperature Thermoplastic UL94V-0; Color Black.
- 1.2 Terminal:Copper Alloy,T=0.12mm.
- 1.3 Shell:Stainless Steel,T=0.20mm.

2.FINISH:

- 2.1 Terminal:Plated Gold on The Contact Area and Solder Tails
- 2.2 Peg:Plated Gold on the bottom of the Solder Tails, Tin Plated over all.

3.SPECIALITY:

- 3.1 Rated current:0.5A
- 3.2 Rated voltage:50V
- 3.3 Contact Resistance:80m Ω MAX
- 3.4 Insulation Resistance:100M Ω MIN 100V DC
- 3.5 Dielectric withstanding voltage: 100V AC.
- 3.6 Solder ability:245 $\pm 5^{\circ}$ C,5 ± 0.5 s.
- 3.7 Operating condition:Temperature: -40° C $\sim +85^{\circ}$ C Humidity: 80% R.H MAX



③	TERMINAL	6	C5210-EH,T=0.12	G/F PLATING
②	BASE INSULATOR	1	LCP+GF30%	BLACK
①	SHELL	1	SUS304-H,T=0.15	AU/Ni PLATING
NO.	PART NAME	Q'TY	DESCRIPTION	NOTE

COSTOMER DRAWING

LAILIAN 深圳市莱联电子有限公司
SHENZHEN LAILIAN ELECTRONICS CO.,LTD

DRAWING	
CHECK	
APPROVAL	

TOLERANCES ARE


30-150	± 0.35	ANGLE $\pm 3^{\circ}$
10-30	± 0.2	
5-10	± 0.15	
0-5	± 0.1	

TITLE SIM卡卡座T1.40 (翻盖式) REV. A

PART NO. LAIL-SIM10-T1.40-F UNITS mm


DWG.NO. Projection

ROHS





NOTES


1. NUMBER OF CONNECTORS:1500PCS/REEL
2. LEAD TAPE LENGTH





3. QUANTITY:15000PCS/CARTON



上下各1PCS珍珠棉



胶纸工字型封箱



COSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO.,LTD			
DRAWING		TITLE SIM卡卡座T1.40（翻盖式） REV. A			
CHECK					
APPROVAL					
TOLERANCES ARE		PART NO. LAIL-SIM10-T1.40-F UNITS mm			
30-150	±0.35				
10-30	±0.2				
5-10	±0.15				
0-5	±0.1				
ANGLE		DWG.NO. Projection			
±3°					