


	REVISIONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2024.08.03	阿树



PART NO.:

X9357 H M-2x01 N2
① ② ③ ④ ⑤

①Series No
②Category:H—HSG
③Welding Board Angle:M—Male HGS
④Row No.—Pin No.:2xXX—2x01P~2x10P,2x12P
⑤Material:N2—PA66 94V—2 White

X9357HM-2x01-N2	PA66	X9357W-A	X9357HF
PART NO	Material	Suitable XBK Wafer	Suitable XBK Housing

	DESIGN	阿树	VIEW:		MODEL TYPE: 4.20 mm Crimp Style Connector
	CHECKED		UNIT:	mm/in	PART NO.: X9357HM-2x01-N2
	APPROVED		SIZE:	A4	DWG NO.: X-X9357HM-2x01-N2
PRECISION CO., LIMITED				SCALE N/A	PAGE 1/1
				REVISION A1	

XK13 星城 Connection

XKB INDUSTRIAL PRECISION CO.,LIMITED

1

2

3

4

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2025.04.01	阿树
/	N/A		/	/	/

A

A

B



B

C

C

D

D




■SPECIFICATIONS

- Voltage rating:600V AC/DC
- Current rating:9A AC/DC
- Withstanding Voltage:1500V AC/minute
- Temperature range:-45°C+125°C
- Insulation resistance:≥1000MΩ
- Contact resistance:≤20mΩ

PART NO.:

X9357 H M-2X01 N2
① ② ③ ④ ⑤

- ①Series No
②Category:H-HSG
③Welding Board Angle:M-Male HGS
④Row No.-Pin No.:2X11P
⑤Material:N2-PA66 94V-2 White



X9357HM-2x01-N2	PA66	X9357W-A	X9357HF
PART NO	Material	Suitable XBK Wafer	Suitable XBK Housing
DESIGN	阿树	VIEW:	MODEL TYPE: 4.20 mm Crimp Style Connector
CHECKED		UNIT: mm/in	PART NO.: X9357HM-2x01-N2
APPROVED		SIZE: A4	DWG NO.: X-X9357HM-2x01-N2
SCALE		PAGE	REVISION
N/A		1/1	A0

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



XKB INDUSTRIAL PRECISION CO.,LIMITED

1

2

3

4