

ROHS





REV.	ECN NO.	DESCRIPTION	DRAW	DATE

MATERIALS

- 1.HOUSING : HI-TEMP PLASTIC LCP-475
- 2.TERMINAL: COPPER ALLOY.
PLATING: GOLD PLATED ON CONTACT AREA,
G/F GOLD PLATED ON SOLDER TAILS.
3. SHELL : STANLESS STEEL.


SPECIFICATION

1. CURRENT RATING : 0.5A MAX.
2. DIELECTRIC WITHSTANDING VOLTAGE :
500V AC R.M.S. FOR 1 MINUTE.
3. INSULATION RESISTANCE : 100M Ω MIN.AT 500V DC.
4. CONTACT RESISTANCE : 50m Ω MAX.
SWITCH RESISTANCE : 100m Ω MAX.
5. OPERATING TEMPERATURE : -30°C TO +85°C.



RECOMMENDED PCB LAYOUT

--- 产品外形 焊盘








PIN ASSIGNMENT	
P1	DAT2
P2	CD/DAT3
P3	CMD
P4	Vod
P5	CLK
P6	Vss
P7	DAT0
P8	DAT1

COSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO.,LTD				
DRAWING						
CHECK						
APPROVAL						
TOLERANCES ARE		TITLE	翻盖式 MicroSD卡 (TF卡) 卡座T1.6	REV.	A	
30-150	±0.35	ANGLE	PART NO.	LAIL-TF03-T1.6-F	UNITS	mm
10-30	±0.2					
5-10	±0.15					
0-5	±0.1					
±3°		DWG.NO.		Projection		

ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE



NOTES:

- 20 SPROCKET HOLE PITCH CUMULATIVE TOLERANCE ± 0.2 .
- MATERIAL: CLARITY CONDUCTIVE POLYSTYRENE ALLOY
100% RECYCLABLE.
- ALL DIMENSIONS MEET EIA-481-3 REQUIREMENTS.
- THICKNESS: 0.25 ± 0.05 MM
- COMPONENT LOAD PER 30.2" REEL: 1000PCS.
- 10REEL/CARTON: 10000PCS

COSTOMER DRAWING		LAILAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO., LTD			
DRAWING					
CHECK					
APPROVAL					
TOLERANCES ARE		TITLE	翻盖式 MicroSD卡 (TF卡) 卡座 T1.6	REV.	A
30-150	± 0.35	ANGLE		PART NO.	LAIL-TF03-T1.6-F
10-30	± 0.2				
5-10	± 0.15				
0-5	± 0.1				
		DWG.NO.		UNITS	mm
				Projection	