

Primary Characteristic

I_O	2*10A
V_{RRM}	150V
I_{FSM}	340A
V_F	0.65V
T_{jmax}	175°C

FEATURES


- Low forward voltage
- High current capability
- High forward surge capability
- Low power losses, High efficiency
- Guarding for over voltage protection

APPLICATIONS


Low VF Schottky barrier rectifier are designed for high frequency, miniature switched mode power supplies such as adapters ,lighting and on-board DC/DC conerters

MECHANICAL DATA


- **Case:** Molded plastic
- **Polarity:** As marked
- **Mounting Position:** Any
- **Molded Plastic:** UL Flammability Classification Rating 94V-0
- Lead free in compliance with EU RoHS 2011/65/EU directive
- Solder bath temperature 275°C maximum,10s per JESD 22-B106




TO-220AB/CT



ITO-220AB/FCT



TO-263/DC



Maximum Ratings (Per Leg) at Ta=25°C unless otherwise specified

Characteristics	Symbol	Value	Unit
Maximum Repetitive Peak Reverse Voltage	V_{RRM}	150	V
Working Peak Reverse Voltage	V_{RWM}	150	V
Maximum DC Blocking Voltage	V_{DC}	150	V
Maximum Average Forward Rectified Current	I_O	10	A
Per Leg		20	
Total			
Peak Forward Surge Current,8.3 ms Single Half Sine-wave Superimposed on Rated Load (JEDEC method)	I_{FSM}	340	A
Operating Temperature Range	T_J	-40 to +175	°C
Storage Temperature Range	T_{STG}	-40 to +150	°C
Typical Thermal Resistance (Note1)	$R_{\theta JC}$	2	°C/W
TO-220AB,TO-263		4	
TO-220F			

Note1: Thermal resistance from Junction to case per leg mounted on heatsink.

Electrical Characteristics (Per Leg) unless otherwise specified

Characteristics		Symbol	Value		Unit
Forward Voltage Drop(Note2)		V _F	Typ.	Max.	V
at I _F =3A	TA=25°C		0.69	-	
	TA=125°C		0.55	-	
at I _F =5A	TA=25°C		0.72	-	
	TA=125°C		0.59	-	
at I _F =10A	TA=25°C		0.78	0.83	
	TA=125°C		0.65	-	
Maximum Reverse Current at V _R =150V	TA=25°C	I _R	0.14	0.5	μA
	TA=125°C		155	-	μA

Note2:Pulse test: 300 μs pulse width, 1 % duty cycle

RATINGS AND CHARACTERISTIC CURVES

FIG.1 MAXIMUM FORWARD CURRENT DERATING CURVE




FIG. 2 MAXIMUM NON-REPETITIVE FORWARD SURGE CURRENT PER LEG




FIG. 3 TYPICAL FORWARD CHARACTERISTICS PER LEG






FIG. 4 TYPICAL REVERSE CHARACTERISTICS PER LEG




Package Outline Dimensions millimeters

TO-220AB



ITO-220AB



TO-263

