





| REVISIONS |         |          |                 |           |        |
|-----------|---------|----------|-----------------|-----------|--------|
| REV.      | ECN NO. | LOCATION | DESCRIPTION     | DATE      | DESIGN |
| A0        | N/A     |          | INITIAL RELEASE | /         | /      |
| A1        | N/A     |          | 图面升级整理图面        | 2025.2.22 | 阿树     |

Specifications:  
规格:  
Voltage rating:250V AC/DC  
额定电压: 250V AC/DC  
Current rating:1A AC/DC  
额定电流: 1A AC/DC  
Withstanding voltage:300V AC/minute  
耐受电压: 300V AC/分钟  
Temperature range:-40℃-+105℃  
温度范围: -40℃-+105℃  
Insulation resistance:≥500MΩ  
绝缘电阻: ≥500MΩ  
Contact resistance:≤20mΩ  
接触电阻: ≤20mΩ  
Material:PA6T UL94V-0  
材质: PA6T UL94V-0  
Plating Category:1U"Gold  
镀层: 1U"Gold  
Wave soldering temperature:255±5℃, 10S  
波峰焊温度: 255±5℃, 10S

PART NO.:  
X1321 W R-2x37 J-C40 D18  
① ② ③ ④ ⑤ ⑥ ⑦  
①Series No  
②Category:W-Wafer  
③Welding Board Angle:R-Stright 90°  
④Row No.Pin No:2xXX-2x01~2x40P  
⑤Plastic Height:J=1.0mm  
⑥Pin Length:C=4.0mm  
⑦Pin Length:D=1.8mm

|                      |    |             |               |                                     |
|----------------------|----|-------------|---------------|-------------------------------------|
| X1321WR-2x37J-C40D18 |    | PA6T        | Brass         | X1321F                              |
| PART NO              |    | Material    | Material(Pin) | Suitable XKB Female                 |
| DESIGN               | 阿树 | VIEW:       |               | MODEL TYPE:<br>1.27mm BTB Connector |
| CHECKED              |    | UNIT: mm/in |               | PART NO.:<br>X1321WR-2x37J-C40D18   |
| APPROVED             |    | SIZE: A4    |               | DWG NO.:<br>X-X1321WR-2x37J-C40D18  |
| SCALE                |    |             | PAGE          | REVISION                            |
| N/A                  |    |             | 1/1           | A1                                  |



P.C.B LAYOUT

|                        |       |
|------------------------|-------|
| AuGLAR                 | ±5°   |
| X.                     | ±0.40 |
| X.x                    | ±0.30 |
| X.xx                   | ±0.20 |
| X.xxx                  | ±0.15 |
| UNSPECIFIED TOLERANCES |       |



XKB INDUSTRIAL PRECISION CO.,LIMITED