








Specifications:

规格:

Voltage rating:350V AC/DC

额定电压: 350V AC/DC

Current rating:3A AC/DC

额定电流: 3A AC/DC

Withstanding voltage:500V AC/minute

耐受电压: 500V AC/分钟

Temperature range:-55℃-+105℃

温度范围: -55℃-+105℃

Insulation resistance:≥1000MΩ

绝缘电阻: ≥1000MΩ

Contact resistance: ≤20mΩ

接触电阻: ≤20mΩ

X1511 H - 09 - N0

① ② ③ ④

1.Series No

2.Category:H-HSG

3.Row No.Pin No:XX-02~10P

4.Material:N0-Nylon 66 UL94V-0 ;

Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C
02	1.50	4.10	3.70	09	12.00	14.60	14.20
03	3.00	5.60	5.20	10	14.0	16.10	15.70
04	4.50	7.10	6.70	11	15.0	17.60	17.20
05	6.00	8.60	8.20	12	17.0	19.10	18.70
06	7.50	10.10	9.70	13	19.0	20.60	20.20
07	9.00	11.60	11.20	14	24.0	22.10	21.70
08	10.50	13.10	12.70	15	24.0	23.60	23.20

X1511H-09-N0	PA66	X1511W	X1511T
PART NO	Material	Suitable XKB Wafer	Suitable XKB Terminal

					ANGLAR	±5°
Δx					L≤ 4	±0.2
Δx					4<L≤ 16	±0.3
Δx					16<L≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L> 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED

}	DSND		SCALE: N/A	MODEL TYPE: 1.5mm Crimp Style Connector		
	DWN		VIEW: 	PART NO.: X1511H-09-N0		
	CHKD		UNIT: mm/in	DWG NO.: X-X1511H-09-N0		
	APPD		SIZE: A4			
L PRECISION CO.,LIMITED				WEIGHT	SHEET 1/1	REVISION A0