

Features/特征

- Size 0.12*0.06 inch /3.2*1.6 mm
- Surface mount resettable fuse
- Voltage rating 6V to 110V
- Current rating from 0.05A to 3.00A
- Fast time-to-trip
- Low resistance
- RoHS compliant, lead-free and halogen-free
- Compatible with high temperature solders

Applications/应用

- USB peripherals
- Plug and play protection for motherboards
- Power tools
- Battery and port protection for smart phones
- Game console port protection
- Set-top-boxes
- Tablets, notebooks, laptops and desktops
- Rechargeable battery packs
- Digital cameras
- Appliances and white goods
- Consumer electronics

Part Number System/产品编号
1206 L 005 / 30 N R L

Electrical Characteristics (25°C)/电性参数

Part Number	Marking	I _{hold} (A)	I _{trip} (A)	V _{max} (Vdc)	I _{max} (A)	P _d typ. (W)	Time to Trip (Max.)		Resistance	
							Current (A)	Time (Sec)	R _{min} (Ω)	R _{1max} (Ω)
1206L001/60NR	BY	0.01	0.05	60	20	0.4	0.10	1.00	15.0	140.0
1206L001/90NR	BY	0.01	0.05	90	20	0.4	0.10	1.00	15.0	140.0
1206L002/60NR	BE	0.02	0.08	60	20	0.4	0.20	1.00	10.0	100.0
1206L002/90NR	BE	0.02	0.08	90	20	0.4	0.20	1.00	10.0	100.0
1206L003/60WR	BX	0.03	0.10	60	20	0.4	0.20	1.20	5.00	70.0
1206L003/90WR	BX	0.03	0.10	90	20	0.4	0.20	1.20	5.00	70.0

Part Number	Marking	I _{hold} (A)	I _{trip} (A)	V _{max} (Vdc)	I _{max} (A)	P _d typ. (W)	Time to Trip (Max.)		Resistance	
							Current (A)	Time (Sec)	R _{min} (Ω)	R _{1max} (Ω)
1206L003/125WR	BX	0.03	0.10	125	20	0.4	0.20	1.20	5.00	70.0
1206L005/30NR	BZ	0.05	0.15	30	40	0.7	0.25	1.50	3.60	50.0
1206L005/60NR	BZ	0.05	0.15	60	100	0.7	0.25	1.50	3.60	50.0
1206L005/72NR	BZ	0.05	0.15	72	40	0.7	0.25	1.50	3.60	50.0
1206L005/85NR	BZ	0.05	0.15	85	40	0.7	0.25	1.50	3.60	50.0
1206L005/90NR	BZ	0.05	0.15	90	40	0.7	0.25	1.50	3.60	50.0
1206L005/110WR	BX	0.05	0.15	110	2	0.7	0.25	1.50	3.60	50.0
1206L010/24NR	BN	0.10	0.25	24	40	0.7	0.50	1.00	1.60	15.0
1206L010/30NR	BN	0.10	0.25	30	40	0.7	0.50	1.00	1.60	15.0
1206L010/33NR	BN	0.10	0.25	33	40	0.7	0.50	1.00	1.60	15.0
1206L010/60NR	BN	0.10	0.25	60	100	0.7	0.50	1.00	1.60	15.0
1206L010/60NRL	BN	0.10	0.25	60	100	0.7	0.50	1.00	1.60	15.0
1206L010/72NR	BN	0.10	0.25	72	40	0.7	0.50	1.00	1.60	15.0
1206L010/85NR	BN	0.10	0.25	85	40	0.7	0.50	1.00	1.60	15.0
1206L010/90NR	BN	0.10	0.25	90	40	0.7	0.50	1.00	1.60	15.0
1206L012/16NR	BN	0.12	0.29	16	40	0.7	0.50	1.00	1.60	13.0
1206L012/30NR	BN	0.12	0.29	30	40	0.7	0.50	1.00	1.60	13.0
1206L012/48NR	BN	0.12	0.29	48	40	0.7	0.50	1.00	1.60	13.0
1206L012/60NR	BN	0.12	0.29	60	100	0.7	0.50	1.00	1.60	13.0
1206L012/72NR	BN	0.12	0.29	72	40	0.7	0.50	1.00	1.60	13.0
1206L012/85NR	BN	0.12	0.29	85	40	0.7	0.50	1.00	1.60	13.0
1206L012/90NR	BN	0.12	0.29	90	40	0.7	0.50	1.00	1.60	13.0
1206L016/16NR	BT	0.16	0.37	16	40	0.7	0.50	0.30	1.00	6.00
1206L016/30NR	BT	0.16	0.37	30	40	0.7	1.00	0.30	1.00	6.00
1206L016/33NR	BT	0.16	0.37	33	40	0.7	1.00	0.30	1.00	6.00
1206L016/48NR	BT	0.16	0.37	48	40	0.7	1.00	0.30	1.00	6.00
1206L016/60NR	BT	0.16	0.37	60	40	0.7	1.00	0.30	1.00	6.00
1206L016/72NR	BN	0.16	0.37	72	40	0.7	1.00	0.30	1.00	6.00
1206L020/16NR	BA	0.20	0.46	16	40	0.8	8.00	0.10	0.35	2.70
1206L020/24NR	BA	0.20	0.46	24	40	0.8	8.00	0.10	0.35	2.70
1206L020/30NR	BA	0.20	0.46	30	40	0.8	8.00	0.10	0.35	2.70
1206L020/33NR	BA	0.20	0.46	33	40	0.8	8.00	0.10	0.35	2.70
1206L020/36NR	BA	0.20	0.46	36	40	0.8	8.00	0.10	0.35	2.70
1206L020/48NR	BA	0.20	0.46	48	40	0.8	8.00	0.10	0.35	2.70
1206L020/54NR	BA	0.20	0.46	54	40	0.8	8.00	0.10	0.35	2.70
1206L020/60NR	BA	0.20	0.46	60	40	0.8	8.00	0.10	0.35	2.70

Part Number	Marking	I _{hold} (A)	I _{trip} (A)	V _{max} (Vdc)	I _{max} (A)	P _d typ. (W)	Time to Trip (Max.)		Resistance	
							Current (A)	Time (Sec)	R _{min} (Ω)	R _{1max} (Ω)
1206L025/6NR	BA	0.25	0.50	6	40	0.8	8.00	0.10	0.35	2.50
1206L025/16NR	BA	0.25	0.50	16	40	0.8	8.00	0.10	0.35	2.50
1206L025/24NR	BA	0.25	0.50	24	40	0.8	8.00	0.10	0.35	2.50
1206L025/30NR	BA	0.25	0.50	30	40	0.8	8.00	0.10	0.35	2.50
1206L025/33NR	BA	0.25	0.50	33	40	0.8	8.00	0.10	0.35	2.50
1206L025/36NR	BA	0.25	0.50	36	40	0.8	8.00	0.10	0.35	2.50
1206L025/48NR	BA	0.25	0.50	48	40	0.8	8.00	0.10	0.35	2.50
1206L025/54NR	BA	0.25	0.50	54	40	0.8	8.00	0.10	0.35	2.50
1206L025/60NR	BA	0.25	0.50	60	40	0.8	8.00	0.10	0.35	2.50
1206L030/16NR	BB	0.30	0.65	16	40	0.8	8.00	0.10	0.25	1.70
1206L030/24NR	BB	0.30	0.65	24	40	0.8	8.00	0.10	0.25	1.70
1206L030/30NR	BB	0.30	0.65	30	40	0.8	8.00	0.10	0.25	1.70
1206L030/33NR	BB	0.30	0.65	33	40	0.8	8.00	0.10	0.25	1.70
1206L030/48NR	BB	0.30	0.65	48	40	0.8	8.00	0.10	0.25	1.70
1206L030/60NR	BB	0.30	0.65	60	40	0.8	8.00	0.10	0.25	1.70
1206L035/6NR	BB	0.35	0.75	6	40	0.8	8.00	0.10	0.25	1.50
1206L035/16NR	BB	0.35	0.75	16	40	0.8	8.00	0.10	0.25	1.50
1206L035/24NR	BB	0.35	0.75	24	40	0.8	8.00	0.10	0.25	1.50
1206L035/30NR	BB	0.35	0.75	30	40	0.8	8.00	0.10	0.25	1.50
1206L035/33NR	BB	0.35	0.75	33	40	0.8	8.00	0.10	0.25	1.50
1206L035/36NR	BB	0.35	0.75	36	40	0.8	8.00	0.10	0.25	1.50
1206L035/48NR	BB	0.35	0.75	48	40	0.8	8.00	0.10	0.25	1.50
1206L035/60NR	BB	0.35	0.75	60	40	0.8	8.00	0.10	0.25	1.50
1206L050/6NR	BF	0.50	1.00	6	100	0.8	8.00	0.10	0.15	0.70
1206L050/8NR	BF	0.50	1.00	8	100	0.8	8.00	0.10	0.15	0.70
1206L050/13.2NR	BF	0.50	1.00	13.2	100	0.8	8.00	0.10	0.15	0.70
1206L050/15NR	BF	0.50	1.00	15	100	0.8	8.00	0.10	0.15	0.70
1206L050/16NR	BF	0.50	1.00	16	100	0.8	8.00	0.10	0.15	0.70
1206L050/24NR	BF	0.50	1.00	24	40	0.8	8.00	0.10	0.15	0.85
1206L050/30NR	BF	0.50	1.00	30	40	1.0	8.00	0.10	0.15	0.85
1206L050/33NR	BF	0.50	1.00	33	40	1.0	8.00	0.10	0.15	0.85
1206L050/36NR	BF	0.50	1.00	36	10	1.0	8.00	0.10	0.15	0.85
1206L050/48NR	BF	0.50	1.00	48	40	1.0	8.00	0.10	0.15	0.85
1206L075/6NR	BG	0.75	1.50	6	100	0.8	8.00	0.20	0.09	0.50
1206L075/8NR	BG	0.75	1.50	8	100	0.8	8.00	0.20	0.09	0.50
1206L075/12NR	BG	0.75	1.50	12	100	0.8	8.00	0.20	0.09	0.50
1206L075/13.2NR	BG	0.75	1.50	13.2	100	0.8	8.00	0.20	0.09	0.50

Part Number	Marking	I _{hold} (A)	I _{trip} (A)	V _{max} (Vdc)	I _{max} (A)	P _d typ. (W)	Time to Trip (Max.)		Resistance	
							Current (A)	Time (Sec)	R _{min} (Ω)	R _{1max} (Ω)
1206L075/16NR	BG	0.75	1.50	16	100	0.8	8.00	0.20	0.09	0.50
1206L075/24NR	BG	0.75	1.50	24	40	1.0	8.00	0.20	0.09	0.50
1206L075/30NR	BG	0.75	1.50	30	40	1.0	8.00	0.20	0.09	0.50
1206L075/33NR	BG	0.75	1.50	33	40	1.0	8.00	0.20	0.09	0.50
1206L075/36NR	BG	0.75	1.50	36	40	1.0	8.00	0.20	0.09	0.50
1206L100/6NR	BH	1.00	1.80	6	100	0.8	8.00	0.30	0.05	0.27
1206L100/12NR	BH	1.00	1.80	12	100	1.0	8.00	0.30	0.05	0.27
1206L100/13.2NR	BH	1.00	1.80	13.2	100	1.0	8.00	0.30	0.05	0.27
1206L100/16NR	BH	1.00	1.80	16	100	1.0	8.00	0.30	0.05	0.27
1206L100/24NR	BH	1.00	1.80	24	40	1.2	8.00	0.30	0.05	0.30
1206L100/30NR	BH	1.00	1.80	30	40	1.2	8.00	0.30	0.05	0.30
1206L100/33NR	BH	1.00	1.80	33	40	1.2	8.00	0.30	0.05	0.30
1206L110/6NR	BH	1.10	2.20	6	100	0.8	8.00	0.30	0.04	0.25
1206L110/12NR	BH	1.10	2.20	12	100	1.0	8.00	0.30	0.04	0.25
1206L110/13.2NR	BH	1.10	2.20	13.2	100	1.0	8.00	0.30	0.04	0.25
1206L110/16NR	BH	1.10	2.20	16	100	1.0	8.00	0.30	0.04	0.25
1206L110/24NR	BH	1.10	2.20	24	40	1.2	8.00	0.30	0.04	0.27
1206L110/30NR	BH	1.10	2.20	30	40	1.2	8.00	0.30	0.04	0.27
1206L110/33NR	BH	1.10	2.20	33	40	1.2	8.00	0.30	0.04	0.27
1206L125/6NR	BI	1.25	2.50	6	100	1.2	8.00	1.00	0.022	0.20
1206L125/16NR	BI	1.25	2.50	16	100	1.2	8.00	1.00	0.022	0.20
1206L125/24NR	BI	1.25	2.50	24	50	1.2	8.00	1.00	0.022	0.20
1206L125/30NR	BH	1.25	2.50	30	50	1.2	8.00	1.00	0.022	0.20
1206L125/33NR	BH	1.25	2.50	33	50	1.2	8.00	1.00	0.022	0.20
1206L150/6NR	BI	1.50	3.00	6	100	0.8	8.00	0.30	0.025	0.130
1206L150/8NR	BI	1.50	3.00	8	100	0.8	8.00	0.30	0.025	0.130
1206L150/12NR	BI	1.50	3.00	12	40	0.8	8.00	0.30	0.025	0.130
1206L150/13.2NR	BI	1.50	3.00	13.2	40	1.0	8.00	0.30	0.025	0.130
1206L150/16NR	BI	1.50	3.00	16	40	1.2	8.00	0.30	0.025	0.130
1206L150/24NR	BI	1.50	3.00	24	40	1.2	8.00	0.30	0.025	0.130
1206L150/30NR	BI	1.50	3.00	30	40	1.2	8.00	0.30	0.025	0.130
1206L175/6NR	BK	1.75	3.30	6	100	1.0	8.00	1.50	0.020	0.115
1206L175/13.2NR	BK	1.75	3.30	13.2	100	1.0	8.00	1.50	0.020	0.115
1206L175/16NR	BL	1.75	3.30	16	40	1.2	8.00	1.50	0.020	0.115
1206L175/24NR	BL	1.75	3.30	24	40	1.2	8.00	1.50	0.020	0.115
1206L200/6NR	BK	2.00	3.50	6	100	1.0	8.00	1.50	0.015	0.080
1206L200/8NR	BK	2.00	3.50	8	100	1.0	8.00	1.50	0.015	0.080

Part Number	Marking	I _{hold} (A)	I _{trip} (A)	V _{max} (Vdc)	I _{max} (A)	P _d typ. (W)	Time to Trip (Max.)		Resistance	
							Current (A)	Time (Sec)	R _{min} (Ω)	R _{1max} (Ω)
1206L200/9NR	BK	2.00	3.50	9	100	1.0	8.00	1.50	0.015	0.080
1206L200/12NR	BK	2.00	3.50	12	100	1.0	8.00	1.50	0.015	0.080
1206L200/13.2NR	BK	2.00	3.50	13.2	100	1.0	8.00	1.50	0.015	0.080
1206L200/16NR	BK	2.00	3.50	16	40	1.2	8.00	1.50	0.015	0.080
1206L200/24NR	BK	2.00	3.50	24	40	1.2	8.00	1.50	0.015	0.080
1206L250/6NR	BP	2.50	5.00	6	35	1.2	8.00	2.00	0.003	0.060
1206L250/12NR	BP	2.50	5.00	12	35	1.2	8.00	2.00	0.003	0.060
1206L250/16AR	BP	2.50	5.00	16	35	1.2	8.00	2.00	0.003	0.060
1206L260/6NR	BP	2.60	5.20	6	100	1.0	8.00	2.00	0.003	0.060
1206L260/12AR	BP	2.60	5.20	12	100	1.0	8.00	2.00	0.003	0.060
1206L260/12NR	BP	2.60	5.20	12	100	1.0	8.00	2.00	0.003	0.060
1206L300/6NR	BP	3.00	6.00	6	100	1.1	8.00	4.00	0.010	0.050
1206L300/8NR	BP	3.00	6.00	8	100	1.1	8.00	4.00	0.010	0.050
1206L300/9NR	BP	3.00	6.00	9	100	1.2	8.00	4.00	0.010	0.050
1206L300/12NR	BP	3.00	6.00	12	100	1.2	8.00	4.00	0.010	0.050

I_{hold} = Hold current: maximum current device will pass without tripping in 25°C still air. 保持电流=在 25°C 静止空气环境中,元件不动作的最大电流。

I_{trip} = Trip current: minimum current at which the device will trip in 25°C still air. 动作电流=在 25°C 静止空气环境中,元件的最小动作电流。

V_{max} = Maximum voltage device can withstand without damage at rated current (I_{max}). 最大电压=元件在额定电流下能承受的最大电压。

I_{max} = Maximum fault current device can withstand without damage at rated voltage (V_{max}). 最大电流=元件在额定电压下能承受的最大电流。

P_{d typ.} = Typical power dissipated from device when in the tripped state at 25°C still air. 动作功率=在 25°C 静止空气环境中,元件动作状态下的消耗功率。


T_{trip} = Maximum time to trip(s) at assigned current reflow soldering of 260°C for 20 sec. 动作时间=5 倍保持电流下的最大动作时间。

R_{min} = Minimum resistance of device in initial (un-soldered) state. 初始最小电阻=元件焊接前的初始最小阻值。

R_{1max} = Maximum resistance of device at 25°C measured one hour after tripping or reflow soldering of 260°C for 20 sec. 焊后最大电阻=元件焊接 1 小时后的最大阻值。

Caution : Operation beyond the specified rating may result in damage and possible arcing and flame. 注意: 超出指定额定值的操作, 可能会导致损伤并可能产生电弧和火焰。

Product Dimensions (mm)/产品尺寸



Part Number	Quantity	A		B		C		D	E
		Min	Max	Min	Max	Min	Max	Min	Min
1206L001/60NR	3500	3.00	3.60	1.50	1.90	0.60	1.20	0.15	0.10

Part Number	Quantity	A		B		C		D	E
		Min	Max	Min	Max	Min	Max	Min	Min
1206L001/90NR	3500	3.00	3.60	1.50	1.90	0.60	1.20	0.15	0.10
1206L002/60NR	3500	3.00	3.60	1.50	1.90	0.60	1.20	0.15	0.10
1206L002/90NR	3500	3.00	3.60	1.50	1.90	0.60	1.20	0.15	0.10
1206L003/60WR	3000	3.00	3.60	1.50	1.90	0.80	1.60	0.15	0.10
1206L003/90WR	3000	3.00	3.60	1.50	1.90	0.80	1.60	0.15	0.10
1206L003/125WR	3000	3.00	3.60	1.50	1.90	0.80	1.60	0.15	0.10
1206L005/30NR	3500	3.00	3.60	1.50	1.90	0.60	1.20	0.15	0.10
1206L005/60NR	3500	3.00	3.60	1.50	1.90	0.60	1.20	0.15	0.10
1206L005/72NR	3500	3.00	3.60	1.50	1.90	0.60	1.20	0.15	0.10
1206L005/85NR	3500	3.00	3.60	1.50	1.90	0.60	1.20	0.15	0.10
1206L005/90NR	3500	3.00	3.60	1.50	1.90	0.60	1.20	0.15	0.10
1206L005/110WR	3000	3.00	3.60	1.50	1.90	0.80	1.60	0.15	0.10
1206L010/24NR	3500	3.00	3.60	1.50	1.90	0.60	1.20	0.15	0.10
1206L010/30NR	3500	3.00	3.60	1.50	1.90	0.60	1.20	0.15	0.10
1206L010/33NR	3500	3.00	3.60	1.50	1.90	0.60	1.20	0.15	0.10
1206L010/60NR	3500	3.00	3.60	1.50	1.90	0.60	1.20	0.15	0.10
1206L010/60NRL	3500	3.00	3.60	1.50	1.90	0.60	1.20	0.15	0.10
1206L010/72NR	3500	3.00	3.60	1.50	1.90	0.60	1.20	0.15	0.10
1206L010/85NR	3500	3.00	3.60	1.50	1.90	0.60	1.50	0.15	0.10
1206L010/90NR	3500	3.00	3.60	1.50	1.90	0.60	1.50	0.15	0.10
1206L012/16NR	3500	3.00	3.60	1.50	1.90	0.60	1.20	0.15	0.10
1206L012/30NR	3500	3.00	3.60	1.50	1.90	0.60	1.20	0.15	0.10
1206L012/48NR	3500	3.00	3.60	1.50	1.90	0.60	1.20	0.15	0.10
1206L012/60NR	3500	3.00	3.60	1.50	1.90	0.60	1.20	0.15	0.10
1206L012/72NR	3500	3.00	3.60	1.50	1.90	0.60	1.20	0.15	0.10
1206L012/85NR	3500	3.00	3.60	1.50	1.90	0.60	1.50	0.15	0.10
1206L012/90NR	3500	3.00	3.60	1.50	1.90	0.60	1.50	0.15	0.10
1206L016/16NR	3500	3.00	3.60	1.50	1.90	0.40	1.20	0.15	0.10
1206L016/30NR	3500	3.00	3.60	1.50	1.90	0.40	1.20	0.15	0.10
1206L016/33NR	3500	3.00	3.60	1.50	1.90	0.40	1.20	0.15	0.10
1206L016/48NR	3500	3.00	3.60	1.50	1.90	0.40	1.20	0.15	0.10
1206L016/60NR	3500	3.00	3.60	1.50	1.90	0.40	1.20	0.15	0.10
1206L016/72NR	3500	3.00	3.60	1.50	1.90	0.40	1.20	0.15	0.10
1206L020/16NR	3500	3.00	3.60	1.50	1.90	0.40	1.00	0.15	0.10
1206L020/24NR	3500	3.00	3.60	1.50	1.90	0.40	1.00	0.15	0.10
1206L020/30NR	3500	3.00	3.60	1.50	1.90	0.40	1.00	0.15	0.10
1206L020/33NR	3500	3.00	3.60	1.50	1.90	0.40	1.00	0.15	0.10
1206L020/36NR	3500	3.00	3.60	1.50	1.90	0.40	1.00	0.15	0.10

Part Number	Quantity	A		B		C		D	E
		Min	Max	Min	Max	Min	Max	Min	Min
1206L020/48NR	3500	3.00	3.60	1.50	1.90	0.60	1.30	0.15	0.10
1206L020/54NR	3500	3.00	3.60	1.50	1.90	0.60	1.30	0.15	0.10
1206L020/60NR	3500	3.00	3.60	1.50	1.90	0.60	1.50	0.15	0.10
1206L025/6NR	3500	3.00	3.60	1.50	1.90	0.40	1.00	0.15	0.10
1206L025/16NR	3500	3.00	3.60	1.50	1.90	0.40	1.00	0.15	0.10
1206L025/24NR	3500	3.00	3.60	1.50	1.90	0.40	1.00	0.15	0.10
1206L025/30NR	3500	3.00	3.60	1.50	1.90	0.40	1.00	0.15	0.10
1206L025/33NR	3500	3.00	3.60	1.50	1.90	0.40	1.00	0.15	0.10
1206L025/36NR	3500	3.00	3.60	1.50	1.90	0.40	1.00	0.15	0.10
1206L025/48NR	3500	3.00	3.60	1.50	1.90	0.50	1.30	0.15	0.10
1206L025/54NR	3500	3.00	3.60	1.50	1.90	0.50	1.30	0.15	0.10
1206L025/60NR	3500	3.00	3.60	1.50	1.90	0.60	1.50	0.15	0.10
1206L030/16NR	3500	3.00	3.60	1.50	1.90	0.40	1.00	0.15	0.10
1206L030/24NR	3500	3.00	3.60	1.50	1.90	0.40	1.00	0.15	0.10
1206L030/30NR	3500	3.00	3.60	1.50	1.90	0.40	1.00	0.15	0.10
1206L030/33NR	3500	3.00	3.60	1.50	1.90	0.40	1.00	0.15	0.10
1206L030/48NR	3500	3.00	3.60	1.50	1.90	0.50	1.30	0.15	0.10
1206L030/60NR	3500	3.00	3.60	1.50	1.90	0.50	1.30	0.15	0.10
1206L035/6NR	3500	3.00	3.60	1.50	1.90	0.40	1.00	0.15	0.10
1206L035/16NR	3500	3.00	3.60	1.50	1.90	0.40	1.00	0.15	0.10
1206L035/24NR	3500	3.00	3.60	1.50	1.90	0.40	1.00	0.15	0.10
1206L035/30NR	3500	3.00	3.60	1.50	1.90	0.40	1.00	0.15	0.10
1206L035/33NR	3500	3.00	3.60	1.50	1.90	0.40	1.20	0.15	0.10
1206L035/36NR	3500	3.00	3.60	1.50	1.90	0.40	1.20	0.15	0.10
1206L035/48NR	3500	3.00	3.60	1.50	1.90	0.50	1.30	0.15	0.10
1206L035/60NR	3500	3.00	3.60	1.50	1.90	0.50	1.30	0.15	0.10
1206L050/6NR	3500	3.00	3.60	1.50	1.90	0.40	1.00	0.15	0.10
1206L050/8NR	3500	3.00	3.60	1.50	1.90	0.40	1.00	0.15	0.10
1206L050/13.2NR	3500	3.00	3.60	1.50	1.90	0.40	1.00	0.15	0.10
1206L050/15NR	3500	3.00	3.60	1.50	1.90	0.40	1.00	0.15	0.10
1206L050/16NR	3500	3.00	3.60	1.50	1.90	0.40	1.00	0.15	0.10
1206L050/24NR	3500	3.00	3.60	1.50	1.90	0.50	1.20	0.15	0.10
1206L050/30NR	3500	3.00	3.60	1.50	1.90	0.50	1.20	0.15	0.10
1206L050/33NR	3500	3.00	3.60	1.50	1.90	0.50	1.20	0.15	0.10
1206L050/36NR	3500	3.00	3.60	1.50	1.90	0.70	1.40	0.15	0.10
1206L050/48NR	3500	3.00	3.60	1.50	1.90	0.50	1.40	0.15	0.10

Part Number	Quantity	A		B		C		D	E
		Min	Max	Min	Max	Min	Max	Min	Min
1206L075/6NR	3500	3.00	3.60	1.50	1.90	0.40	1.00	0.15	0.10
1206L075/8NR	3500	3.00	3.60	1.50	1.90	0.40	1.00	0.15	0.10
1206L075/12NR	3500	3.00	3.60	1.50	1.90	0.40	1.00	0.15	0.10
1206L075/13.2NR	3500	3.00	3.60	1.50	1.90	0.40	1.00	0.15	0.10
1206L075/16NR	3500	3.00	3.60	1.50	1.90	0.40	1.00	0.15	0.10
1206L075/24NR	3500	3.00	3.60	1.50	1.90	0.60	1.60	0.15	0.10
1206L075/30NR	3500	3.00	3.60	1.50	1.90	0.60	1.60	0.15	0.10
1206L075/33NR	3500	3.00	3.60	1.50	1.90	0.60	1.60	0.15	0.10
1206L075/36NR	3500	3.00	3.60	1.50	1.90	0.60	1.60	0.15	0.10
1206L100/6NR	3500	3.00	3.60	1.50	1.90	0.50	1.60	0.15	0.10
1206L100/12NR	3500	3.00	3.60	1.50	1.90	0.50	1.60	0.15	0.10
1206L100/13.2NR	3500	3.00	3.60	1.50	1.90	0.50	1.60	0.15	0.10
1206L100/16NR	3500	3.00	3.60	1.50	1.90	0.50	1.60	0.15	0.10
1206L100/24NR	3500	3.00	3.60	1.50	1.90	0.50	1.60	0.15	0.10
1206L100/30NR	3500	3.00	3.60	1.50	1.90	0.50	1.60	0.15	0.10
1206L100/33NR	3500	3.00	3.60	1.50	1.90	0.60	1.60	0.15	0.10
1206L110/6NR	3500	3.00	3.60	1.50	1.90	0.50	1.60	0.15	0.10
1206L110/12NR	3500	3.00	3.60	1.50	1.90	0.50	1.60	0.15	0.10
1206L110/13.2NR	3500	3.00	3.60	1.50	1.90	0.50	1.60	0.15	0.10
1206L110/16NR	3500	3.00	3.60	1.50	1.90	0.50	1.60	0.15	0.10
1206L110/24NR	3500	3.00	3.60	1.50	1.90	0.50	1.60	0.15	0.10
1206L110/30NR	3500	3.00	3.60	1.50	1.90	0.50	1.60	0.15	0.10
1206L110/33NR	3500	3.00	3.60	1.50	1.90	0.60	1.60	0.15	0.10
1206L125/6NR	3500	3.00	3.60	1.50	1.90	0.50	1.60	0.15	0.10
1206L125/16NR	3500	3.00	3.60	1.50	1.90	0.50	1.60	0.15	0.10
1206L125/24NR	3500	3.00	3.60	1.50	1.90	0.50	1.60	0.15	0.10
1206L125/30NR	3500	3.00	3.60	1.50	1.90	0.50	1.60	0.15	0.10
1206L125/33NR	3500	3.00	3.60	1.50	1.90	0.60	1.60	0.15	0.10
1206L150/6NR	3500	3.00	3.60	1.50	1.90	0.50	1.60	0.15	0.10
1206L150/8NR	3500	3.00	3.60	1.50	1.90	0.50	1.60	0.15	0.10
1206L150/12NR	3500	3.00	3.60	1.50	1.90	0.50	1.60	0.15	0.10
1206L150/13.2NR	3500	3.00	3.60	1.50	1.90	0.50	1.60	0.15	0.10
1206L150/16NR	3500	3.00	3.60	1.50	1.90	0.50	1.60	0.15	0.10
1206L150/24NR	3500	3.00	3.60	1.50	1.90	0.50	1.60	0.15	0.10
1206L150/30NR	3500	3.00	3.60	1.50	1.90	0.50	1.60	0.15	0.10
1206L175/6NR	3500	3.00	3.60	1.50	1.90	0.70	1.60	0.15	0.10

Part Number	Quantity	A		B		C		D	E
		Min	Max	Min	Max	Min	Max	Min	Min
1206L175/13.2NR	3500	3.00	3.60	1.50	1.90	0.70	1.60	0.15	0.10
1206L175/16NR	3500	3.00	3.60	1.50	1.90	0.70	1.60	0.15	0.10
1206L175/24NR	3500	3.00	3.60	1.50	1.90	0.70	1.60	0.15	0.10
1206L200/6NR	3500	3.00	3.60	1.50	1.90	0.70	1.60	0.15	0.10
1206L200/8NR	3500	3.00	3.60	1.50	1.90	0.70	1.30	0.15	0.10
1206L200/9NR	3500	3.00	3.60	1.50	1.90	0.70	1.30	0.15	0.10
1206L200/12NR	3500	3.00	3.60	1.50	1.90	0.70	1.60	0.15	0.10
1206L200/13.2NR	3500	3.00	3.60	1.50	1.90	0.70	1.60	0.15	0.10
1206L200/16NR	3500	3.00	3.60	1.50	1.90	0.70	1.60	0.15	0.10
1206L200/24NR	3500	3.00	3.60	1.50	1.90	0.70	1.60	0.15	0.10
1206L250/6NR	3500	3.00	3.60	1.50	1.90	0.70	1.60	0.15	0.10
1206L250/12NR	3500	3.00	3.60	1.50	1.90	0.70	1.60	0.15	0.10
1206L250/16AR	4000	3.00	3.50	1.50	1.85	0.70	1.20	0.15	0.10
1206L260/6NR	3500	3.00	3.60	1.50	1.90	0.70	1.60	0.15	0.10
1206L260/12AR	4000	3.00	3.60	1.50	1.90	0.70	1.20	0.15	0.10
1206L260/12NR	3500	3.00	3.60	1.50	1.90	0.70	1.60	0.15	0.10
1206L300/6NR	3500	3.00	3.60	1.50	1.90	0.70	1.60	0.15	0.10
1206L300/8NR	3500	3.00	3.60	1.50	1.90	0.70	1.60	0.15	0.10
1206L300/9NR	3500	3.00	3.60	1.50	1.90	0.70	1.60	0.15	0.10
1206L300/12NR	3500	3.00	3.60	1.50	1.90	0.70	1.60	0.15	0.10


Environmental Specifications/环境规范

Test 测试项目	Conditions 条件	Resistance change 电阻变化
Resistance to solvent 抗溶剂性能	MIL-STD-202, Method 215	No change
Vibration 抗震性	MIL-STD-202, Method 201	No change
Ambient operating conditions : - 40 °C to +85 °C 工作环境温度		
Maximum surface temperature of the device in the tripped state is 125°C. 保护状态下的元件表面最高温度为 125°C		


Temperature Derating/不同环境温度下的 I_{hold} 值

Part Number	Ambient operating temperature hold current (I_{hold})								
	-40℃	-20℃	0℃	25℃	40℃	50℃	60℃	70℃	85℃
1206L001	0.015	0.013	0.012	0.010	0.009	0.008	0.007	0.006	0.0058
1206L002	0.030	0.026	0.023	0.020	0.017	0.015	0.014	0.012	0.010
1206L003	0.045	0.040	0.035	0.030	0.026	0.023	0.021	0.018	0.015
1206L005	0.074	0.066	0.056	0.050	0.042	0.037	0.035	0.030	0.027
1206L010	0.148	0.132	0.116	0.100	0.085	0.075	0.070	0.060	0.055
1206L012	0.18	0.16	0.14	0.12	0.10	0.09	0.08	0.07	0.06
1206L016	0.24	0.21	0.18	0.16	0.14	0.13	0.12	0.09	0.08
1206L020	0.30	0.26	0.23	0.20	0.17	0.15	0.14	0.12	0.11
1206L025	0.37	0.33	0.29	0.25	0.22	0.20	0.17	0.15	0.12
1206L030	0.44	0.39	0.35	0.30	0.26	0.24	0.20	0.18	0.14
1206L035	0.50	0.45	0.40	0.35	0.30	0.27	0.24	0.21	0.15
1206L050	0.71	0.64	0.57	0.50	0.42	0.39	0.35	0.31	0.25
1206L075	1.14	1.01	0.88	0.75	0.65	0.59	0.54	0.49	0.41
1206L100	1.45	1.31	1.15	1.00	0.84	0.77	0.69	0.61	0.48
1206L110	1.60	1.45	1.30	1.10	0.95	0.80	0.72	0.66	0.55
1206L125	2.05	1.79	1.58	1.25	1.13	0.91	0.85	0.78	0.64
1206L150	2.18	1.94	1.72	1.50	1.28	1.17	1.06	0.96	0.77
1206L175	2.34	2.05	1.89	1.75	1.44	1.31	1.20	1.00	0.82
1206L200	2.88	2.63	2.34	2.00	1.74	1.58	1.42	1.17	0.93
1206L250	3.38	3.17	2.85	2.50	2.17	1.96	1.73	1.48	1.22
1206L260	3.43	3.22	2.93	2.60	2.23	2.03	1.87	1.57	1.35
1206L300	4.05	3.66	3.36	3.00	2.50	2.28	2.00	1.62	1.38


Derating Curve/环境温度与工作电流关系特性图



Typical Time-to-Trip at 25°C/25°C跳闸保护时间曲线





Soldering Parameters/焊接参数



- Recommended reflow methods: IR, vapor phase oven, hot air oven, N₂ environment for lead-free;
推荐的回流方法：红外光谱，气相炉，热空气炉中，氮气环境，无铅焊接；
 - Recommended maximum paste thickness is 0.25mm;
推荐刷锡厚度最大为 0.25mm；
 - Devices can be cleaned using standard industry methods and solvents;
产品可以使用行业标准的方法和溶剂清洗；
- Note 1:** All temperature refer to topside of the package, measured on the package body surface;
注 1：所有的温度是在焊接时，在产品上所测量出来；
- Note 2:** If reflow temperatures exceed the recommended profile, devices may not meet the performance requirements.
注 2：如果回流温度超过推荐参数要求，产品可能无法满足性能要求。

Profile Feature 特征		Pb-Free Assembly 无铅焊锡
Average Ramp-Up Rate (T _{s(max)} to T _p) 平均升温速度		3°C/second max
Preheat 预热	-Temperature Min(T _{s(min)}) 最低温度	150°C
	-Temperature Max(T _{s(max)}) 最高温度	200°C
	-Time(T _{s(min)} to T _{s(max)}) 预热时间	60~180 seconds
Time maintained above: 保持时间	-Temperature(T _L) 温度	217°C
	-Time(t _L) 时间	60~150 seconds
Peak Temperature (T _p) 峰值温度		260°C
Time within 5°C of actual Peak : Temperature (tp)		20-40 seconds
Ramp-Down Rate 降温		6°C/second max
Time 25°C to Peak Temperature 从 25°C到峰值温度时间		8 minutes max
Storage Condition 储存条件		0°C~30°C 30%-60%RH

Tape And Reel Specifications (mm)/料带和卷



Reel Dimensions 卷盘规格	
C	φ178 ± 1.0
D	φ60.2 ± 0.5
H	11.0 ± 0.5
W	9.0 ± 1.5

Governing Specifications 料带规格	1206L001 ~ 1206L075, 1206L100/6NR ~ 1206L100/16NR, 1206L110/6NR ~ 1206L110/16NR, 1206L125, 1206L150, 1206L250/16AR	1206L020/60NR, 1206L025/60NR, 1206L100/24NR ~ 1206L100/33NR, 1206L110/24NR ~ 1206L110/33NR, 1206L150/13.2NR/16NR 1206L175 ~ 1206L300	1206L003/60WR, 1206L003/90WR, 1206L003/125WR
W	8.0 ± 0.3	8.0 ± 0.3	8.0 ± 0.3
F	3.5 ± 0.05	3.5 ± 0.05	3.5 ± 0.05
E1	1.75 ± 0.1	1.75 ± 0.1	1.75 ± 0.1
D0	1.55 ± 0.05	1.55 ± 0.05	1.55 ± 0.05
D1	1.0 ± 0.1	1.0 ± 0.1	1.0 ± 0.1
P0	4.0 ± 0.1	4.0 ± 0.1	4.0 ± 0.1
P1	4.0 ± 0.1	4.0 ± 0.1	4.0 ± 0.1
P2	2.0 ± 0.05	2.0 ± 0.05	2.0 ± 0.05
A0	1.95 ± 0.1	1.95 ± 0.1	1.95 ± 0.1
B0	3.65 ± 0.1	3.65 ± 0.1	3.65 ± 0.1
T	0.2 ± 0.1	0.2 ± 0.1	0.2 ± 0.1
K0	1.04 ± 0.1	1.35 ± 0.1	1.50 ± 0.1
Leader _{min}	390	390	390
Trailer _{min}	160	160	160

WARNING

- Users shall independently assess the suitability of these devices for each of their applications.
- Users shall independently assess the suitability of these devices for each of their applications.
- Operation of these devices beyond the stated maximum ratings could result in damage to the devices and lead to electrical arcing and/or fire.
- These devices are intended to protect against the effects of temporary over-current or over-temperature Conditions and are not intended to perform as protective devices where such conditions are expected to be repetitive or prolonged in duration.
- Exposure to silicon-based oils, solvents, electrolytes, acids, and similar materials can adversely affect the prolonged of these PPTC devices.
- These devices undergo thermal expansion under fault conditions, and thus shall be provided with adequate space and be protected against mechanical stresses.
- Circuits with inductance may generate a voltage (L di/dt) above the rated voltage of the PPTC device.

Cautions for SMD PPTC Use/贴片 PPTC 使用注意事项

1. PTC Device is a resettable overcurrent circuit protection device used to protect against overcurrent faults in electronic circuits. It cannot be used as a switch, and multiple times tripping will reduce the PTC hold current.

PTC 器件是一种可复位的过流电路保护元件，用于保护电子电路中的过流故障。不能作为开关使用，重复多次保护会降低 PTC 的维持电流。

2. The PTC is a thermally sensitive device with a positive temperature coefficient which means that the resistance increases with increasing temperature. It is recommended to keep away from heat source devices when designing to minimize the influence of external heat sources.

PTC 是一种具有正温度系数的热敏器件，即电阻随温度升高而增大。设计时建议远离热源器件，尽量减少外部热源的影响。

3. This product should not be used in an application where the maximum voltage or maximum current can be exceeded in a fault condition. Operation beyond the maximum ratings or improper use may result in device damage and possible electrical arcing and flame.

本产品不应用于在故障条件下可能超过最大电压或最大电流的应用中。超出最大额定值的操作或不当使用可能会导致 PTC 损坏，出现电弧现象，甚至烧毁。

4. Hold current at all temperature specified in the specification is the conventional performance of PTC obtained by one reflow soldering. It can hold 1 hour under the current conditions corresponding to different temperatures. This current is not the condition of long-term charging or discharging current for this type of PTC.

规格书中所规定的各温度下的维持电流是 PTC 通过一次回流焊接后获得的常规性能。PTC 在不同温度对应的当前电流条件下可保持 1 小时。该电流并不是该型号 PTC 能够适应的长期充电或放电电流的条件。

5. The resistance and other electrical parameters indicated in the specification are all based on the test results of the manufacturer's designated test board by one reflow soldering. If there is any further heat generated process like multiple soldering, injection molding, dispensing, the product parameters will decrease at certain degree. Therefore the verification test to be conducted is necessary.

规格书中的电阻等电气参数均以厂家指定测试板一次回流焊的测试结果为准。如果有进一步的发热过程，如多次焊接、注塑、点胶等，产品参数会有所衰减。因此需要进行验证测试其适用性。

6. SMD PTC is designed for the SMT process which applies reflow soldering. For reflow soldering, please refer to the recommended curve diagram. If the recommended value is exceeded, the internal resistance of PTC may increase. Hand soldering is not recommended and heat gun is not allowed to use during the circuit boards rework. If there is soldering iron welding process, it is recommended that the welding position should be more than 1.5mm away from PTC, the welding temperature should be lower than 350°C, and the contact time with the solder joint should not exceed 3 seconds.

SMD PTC 是为采用回流焊接的 SMT 工艺设计的。焊接工艺请参考厂家推荐的回流焊曲线图。如果超过推荐值，PTC 的内阻可能会增加并受到损伤。禁止使用手工焊接，禁止电路板返工时使用热风枪。如果有烙铁焊接工艺，建议焊接位置离 PTC 1.5mm 以上，焊接温度低于 350°C，与焊点接触时间不超过 3 秒。

7. When mounting or using PTC, all injection molding materials, curing adhesives, UV glue, silica gel and cleaning agents or solvents must be tested in terms of application parameters e.g. temperature, time, and etc to ensure the consistency between the product and the processing before use.

贴装或应用 PTC 时，所有注塑材料、固化粘合剂、UV 胶、硅胶和清洁剂或溶剂都必须在应用参数方面进行测试，例如温度、时间等，以保证产品及工艺的匹配性，确认不会影响 PTC 性能之后方可使用。

8. When mounting or using PTC, it is not recommended to use circuit board washer water or other cleaning agent. If cleaning is required, it is necessary to verify the applicability of various cleaning agents, washboard water and solvents, and confirm that they will not affect the PTC performance. The known chemicals that impacts PTC include but not limited to ethers, benzene homolog, ketones, lipids and derivatives that is of strong solubleness and ruinous. Please place the product in open environment for at least 24 hours to volatilize solvents residuals.

贴装或应用 PTC 时，不建议使用电路板清洗水或其他清洁剂。如果需要清洗时，需要验证各种清洗剂、洗板水和溶剂的适用性，并确认它们不会影响 PTC 性能。已知的影响 PTC 的化学药品包括但不限于醚类、苯同系物、酮类、脂类和具有强溶解性和破坏性的有机化合物。清洗后请将产品放置在开放环境中至少 24 小时以充分挥发溶剂残留物。

9. When PTC is welded to the PCB in product application, if injection or gluing is needed, it should be completed in as short a time as possible. If the time slot between mounting and injection or gluing surpasses 1 month, please keep in airtight environment to avoid long air exposure.

产品应用中 PTC 焊接到 PCB 后，如需注胶或胶合，应在尽可能短的时间内完成。如果贴装和注塑或涂胶之间的时间间隔超过 1 个月，请密封保存，避免 PTC 长时间暴露在空气中。

10. In charging terminal application, PP type material is recommended to use as inner membrane and TPE and PVC type material is inhibited.

PTC 在充电终端应用中，建议使用 PP 类材料作为内膜，禁止使用 TPE 类和 PVC 类材料。

11. LUTE SMD PTC humidity sensitivity grade 2, for sealed packaging. If customers find damaged packaging in stock, they should isolate the product immediately. If there is any surplus material, they needs to be restored to the previous packaging state and do sealed storage.

陆特 SMD PTC 湿敏度为 2 级且为密封包装。如果客户发现库存中包装损坏，应立即将产品隔离。使用时如有余料，需恢复成之前的包装状态，并且密封保存。