

**High Efficiency Glass Passivated Rectifiers****Reverse Voltage - 50 to 1000 Volts
Forward Current - 2.0 Ampere****Features**

- Low cost
- Ultra fast switching for high efficiency
- Low reverse leakage current
- Low forward voltage drop
- High current capability
- The plastic material carries UL recognition 94V-0


Mechanical Data

- Case: JEDEC DO-15 Molded plastic
- Polarity: Color band denotes cathode
- Mounting position: Any

Note: Products with logo  or  are made by HY Electronic (Cayman) Limited.

Applications

- For use in SMPS, high frequency inverters, PWM and polarity protection applications

DO-15

Package Outline Dimensions in Inches (Millimeters)

**RoHS
COMPLIANT****Maximum Ratings and Electrical Characteristics**

Rating at 25°C ambient temperature unless otherwise specified.

Single phase, half wave, 60Hz, resistive or inductive load.

For capacitive load, derate current by 20%.

Characteristics	Symbol	HER 201G	HER 202G	HER 203G	HER 204G	HER 205G	HER 206G	HER 207G	HER 208G	Unit
		UF 2001G	UF 2002G	UF 2003G	UF 2004G	UF 2005G	UF 2006G	UF 2007G	UF 2008G	
Maximum Repetitive Peak Reverse Voltage	VRRM	50	100	200	300	400	600	800	1000	V
Maximum RMS Voltage	VRMS	35	70	140	210	280	420	560	700	V
Maximum DC Blocking Voltage	VDC	50	100	200	300	400	600	800	1000	V
Maximum Average Forward Rectified Current @TA=50 °C	I(AV)	2.0								A
Peak Forward Surge Current, 8.3mS Single Half Sine-Wave, Superimposed on Rated Load (JEDEC Method)	IFSM	60								A
Peak Forward Voltage at 2.0 A DC	VF	1.0			1.3		1.7			V
Maximum DC Reverse Current at Rated @TJ=25°C	IR	5.0								µA
DC Blocking Voltage @TJ=100°C		100								
Maximum Reverse Recovery Time (Note 1)	TRR	50					75			nS
Typical Junction Capacitance (Note2)	CJ	50					30			pF
Typical Thermal Resistance Junction to Ambient	RθJA	25								°C/W
Operating Junction Temperature Range	TJ	-55 to +150								°C
Storage Temperature Range	TSTG	-55 to +150								°C

Notes:1.Measured with I_F=0.5A,I_R=1A,IRR=0.25A.

2.Measured at 1.0 MHz and applied reverse voltage of 4.0V DC.

3.The typical data above is for reference only.



Fig. 1 - Forward Current Derating Curve




Fig. 2 - Maximum Non-Repetitive Surge Current




Fig. 3 - Typical Junction Capacitance




Fig. 4 - Typical Forward Characteristics




Fig. 5 - Typical Forward Characteristics





Fig. 6 - Typical Forward Characteristics





Disclaimer

ALL specifications and data are subject to be changed without notice to improve reliability function or design or other reasons.

HY makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, HY disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on HY's knowledge of typical requirements that are often placed on HY products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify HY's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, HY products are not designed for use in medical, life-saving, or life-sustaining applications or for any other applications in which the failure of the HY product could result in personal injury or death. Customers using or selling HY products not expressly indicated for use in such applications do so at their own risk. Please contact authorized HY personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of HY. Product names and markings noted herein may be trademarks of their respective owners.