







01:AU 1U"Min			
03:AU 3U"Min	1:PBT	W:WHITE	
05:AU 5U"Min	2:PA6T	B:BLACK	
10:AU 10U"Min	3:PA9T		
15:AU 15U"Min	4:LCP		
30: AU 30U"Min			

L	
1	8.17
2	9.17

					ANGLAR	±5°
Δx					L ≤ 4	±0.2
Δx					4 < L ≤ 16	±0.3
Δx					16 < L ≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L > 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dq.cn						



XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND		SCALE: N/A	MODEL TYPE: Type-C 3.1		
DWN		VIEW: 	PART NO.: U262-243N-3BVC80-1		
CHKD		UNIT: mm/in	DWG NO.: X-U262-243N-3BVC80-1		
APPD		SIZE: A4			
L PRECISION CO.,LIMITED			WEIGHT	SHEET	REVISION
				1/1	A0