

Medical
electric
equipmentPower
Factor
CorrectionWorld
wideSafety
Approvals

EMI

Inrush
current
limiting

OCP




OVP

Remote
ON/OFFParallel
Operation

1U

G-series



■ Features

ROHS Compliant (pb free)

Meets or exceeds IEEE802.3 standards including 350uH Min OCL with 8mADC

High performance for EMI suppression , Crosstalk, Return loss

Minimum 2250VDC insulation per IEEE802.3 requirement

Minimize PCB space and Simplify PCB Layout

Less magnetic components to be placed on PCB, higher reliability and yields

Operating temperature: 0°C~+70°C

Storage temperature: -40°C~+85°C






■ ROHS REACH marking

■ CE FCC marking

2.Mechanical Dimensions:

Yellow LED
Left LED

Green LED
Right LED



All dimension tolerance are ± 0.08 unless otherwise specified

3. Specifications

Electrical Specification@25° C Operating Temperature 0 to +70° C							
Part NO	OCL primary@100KHz 0.1Vms 8mA	Leakage primary@10KHz 0.1Vms	LED Specification				
			Standard LED	Wavelength	Forward V(Min/Max)	Forward A	Type
GTA14DRJ01	350uH Min	0.5uH max	Green	568nm	1.7v/2.6v	20mA	squareness
			Yellow	585nm	1.7v/2.6v	20mA	squareness

Electrical Specification@25° C Operating Temperature 0 to +70° C									
Part NO	Insertion loss(dB max) 1-100MHz	Return Loss(db min)MHz				DMRR(dB min)MHz		Crosstalk(dB min)MHz	Isolation Voltage(Vrms min)
		1-30	40	50	60-100	1-60	60-100	1-100	
GTA14DRJ01	-1.0	-20	-16	-16	-12	-50	-50	-30	2250

4.Schematic&LED

