







Recommended P.C.B Layout(Top Side)  
(PCB BOARD TOLERANCE±0.05)



SPECIFICATIONS  
Rated Current:1.0AMP  
Contact Resistance:20mΩ Max  
Withstand Voltage:500V AC/DC  
Insulation Resistance:1000MΩ Min  
Operation Temperature:-40°c to +105°c

Contact Material:Phosphor Bronze  
Contact Plating:Au Over Ni  
Insulator Material:Polyester(UL94V-0)  
Standard: PA9T  
Max.Processing Temp: 230°C for 30-60 seconds  
(260°C for 10 seconds)

### Ordering Information

| No. of Rows  | No. of Pins | Type | Length (Plastic) | Contact      | Plating   | Post |
|--------------|-------------|------|------------------|--------------|-----------|------|
| 1=Single Row | 2=40Pin     | 2=带针 |                  | G0:Gold      | Flash     |      |
| 2=Dual Row   |             | 3=带针 |                  | G1:1u" Gold  | +Cap      | (带柱) |
|              |             | 4=带针 |                  | G2:3u" Gold  |           |      |
|              |             |      |                  | G3:5u" Gold  |           |      |
|              |             |      |                  | G4:10u" Gold |           |      |
|              |             |      |                  | G5:15u" Gold |           |      |
|              |             |      |                  | G6:30u" Gold |           |      |
|              |             |      |                  | S0:Gold      | Flash/Tin |      |
|              |             |      |                  | S1:Tin       |           |      |

|           |                        |                    |                   |       |                   |                                                                                       |                  |                      |              |     |
|-----------|------------------------|--------------------|-------------------|-------|-------------------|---------------------------------------------------------------------------------------|------------------|----------------------|--------------|-----|
|           |                        |                    | GENERAL TOLERANCE |       | 制 图<br>DRAWING    | 深圳市华灿天禄电子有限公司<br>ShenzhenhuacantianluELECTRONICS CO.,LTD                              |                  |                      |              |     |
|           |                        |                    | DIM               | TOL   | 审 核<br>CHECK      |                                                                                       |                  |                      |              |     |
|           |                        |                    | X. X              | ±0.30 | 批 准<br>APPROVAL   |                                                                                       | 产品名称<br>TITLE    | 1.27双排 排母 贴片 带盖      | 版 本<br>REV.  | A   |
|           |                        |                    | X. XX             | ±0.20 |                   |                                                                                       |                  |                      |              |     |
| 1         | 初版发行                   |                    | X. XXX            | ±0.10 | 比 例<br>SCALE      |                                                                                       | 产品料号<br>PART NO. | PM127-2-N-S-4.3-XX-R | 单 位<br>UNITS | mm  |
| 序号<br>No. | 变更内容<br>MODIFY CONTENT | 日 期<br>MODIFY DATE | Angle             | ±3.0° | 投 影<br>Projection |  | 材 料<br>MATERIAL  |                      | 页 次<br>SHEET | 1/1 |