




PCB LAYOUT

Specifications:

规格:

Voltage rating: 250V AC/DC

额定电压: 250V AC/DC

Current rating: 1A AC/DC

额定电流: 1A AC/DC

Withstanding voltage: 300V AC/minute

耐受电压: 300V AC/分钟

Temperature range: -40°C ~ +105°C

温度范围: -40°C ~ +105°C

Insulation resistance: ≥500MΩ

绝缘电阻: ≥500MΩ

Contact resistance: ≤20mΩ

接触电阻: ≤20mΩ

Material: PA6T UL94V-0

材质: PA6T UL94V-0

Plating Category: 1U" Gold

镀层: 1U" Gold

Wave soldering temperature: 255±5°C, 10S

波峰焊温度: 255±5°C, 10S

X1322	W	R	- 2x09	K -	C40	D30 -	E14	F06
①	②	③	④	⑤	⑥	⑦	⑧	⑨

- Series No.
- Category: W-Water
- Welding Board Angle: R-Stright 90°
- Row No - Pin No: 2xXX-2x02P-2x40P
- Plastic height: K=1.5mm
- Pin length: C=4.0mm
- Pin length: D=3.0mm
- Pin length: E=1.45mm
- Pin length: F=0.6mm

X1322WR-2x09K-C40D30-E14F06	PA6T	Brass	1U"Gold	X1321F
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB Female

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
ΔX					ANGULAR ±5°
ΔX					L ≤ 4 ±0.2
ΔX					4 < L ≤ 16 ±0.3
ΔX					16 < L ≤ 63 ±0.4
ΔX					L > 63 ±0.5
REVISIONS					
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn					

XKB

XKB INDUSTRIAL PRECISION CO., LIMITED

DSND	SCALE: N/A	MODEL TYPE:
DWN	VIEW:	1.27mm BTB Connector
CHKD	UNIT: mm/in	PART NO.: X1322WR-2x09K-C40D30-E14F06
APPD	SIZE: A4	DWG NO.: X-X1322WR-2x09K-C40D30-E14F06
		WEIGHT
		SHEET 1/1
		REVISION A0