


Specification Sheet



Terminal Pad Solderability

Meets EIA Specification RS186-9E
And ANSI/J-STD-002 Category 3.

Terminal Pad Materials

Tin-Plated Nickel-Copper
Solder Material: Matte Tin (Sn)
Lead-Free, RoHS Compliant

Marking

Part Identification
ASMD1210SL300-21V = JL

Recommended Pad layout(mm)

Physical Dimensions(mm.)

Model	A		B		C		D		E
	Min.	Max.	Min.	Max.	Min.	Max.	Min.	Max.	Min.
ASMD1210SL300-21V	3.00	3.43	2.35	2.80	0.60	1.00	0.25	0.75	0.10


Electrical Characteristics

Model	I _{hold} @25°C (A)	I _{hold} @70°C (A)	V _{max} (V)	I _{max} (A)	P _d Typ. (W)	Thermal Cut Off (°C)		Resistance	
						3A		R _{i min} (Ω)	R _{1max} (Ω)
						Min.	Max.		
ASMD1210SL300-21V	3.00	1.85	21.0	15.0	1.5	70	100	0.003	0.020

Thermal Derating Chart

Model	Maximum ambient operating temperature (T _{mao}) vs. hold current (I _{hold})									
	- 40°C	- 20°C	0°C	20°C	25°C	40°C	50°C	60°C	70°C	85°C
ASMD1210SL300-21V	4.40	4.00	3.50	3.15	3.00	2.70	2.30	2.15	1.85	1.40

Soldering Parameters



Profile Feature	Pb-Free Assembly
Average Ramp-Up Rate(Ts _{Max} to Tp)	3°C/s Max.
-Temperature Min(Ts _{Min})	150°C
Preheat -Temperature Max(Ts _{Max})	200°C
-Time(ts _{Min} to ts _{Max})	60~180 s
Time maintained -Temperature(TL)	217°C
above: -Time(tL)	60~150 s
Peak/Classification Temperature(Tp)	260+0/-5°C
Time within 5°C of actual peak temperature(tp)	20~40 s
Ramp down rate	6°C/s Max.
Time 25°C to peak temperature	8 min. Max.

- ◆ All temperature refer to topside of the package, measured on the package body surface
- ◆ If reflow temperature exceeds the recommended profile, devices may not meet the performance requirements
- ◆ Recommended reflow methods: IR, vapor phase oven, hot air oven, N2 environment for lead
- ◆ Recommended maximum paste thickness is 0.25mm (0.010inch)
- ◆ Devices can be cleaned using standard industry methods and solvents

Packaging Quantity

Model	Quantity
ASMD1210SL300-21V	4,000 pcs/reel