


1. Configuration and Dimensions (Unit:m/m)



Type	A	B	C	D1	D2	Q`TY/REEL
AACM3225	3.2±0.2	2.5±0.2	2.2±0.2	0.75	0.9	1500

2. Part Number Code

AACM	3225	T	102	W2H
Series Name	Dimensions	Tolerance ±25%	Impedance	Internal controls

3. Electrical Characteristics

Part Number	Common-Mode ImpedanceZ (Ω)at 100MHz	Resistance Rdc(Ω) Max.	Rated Current (mA)Max.	Rated Voltage Vdc(V)Max.	Withstandin g Voltage Vode(V)Max.	Insulation Resistance (Ω)Min.
AACM3225T102W2H	1000	0.1	1500	80	125	10M

Notes:

- 1) AEC-Q200 qualified.
- 2) All test data is referenced to 25°C ambient.
- 3) Operating temperature range -40°C to +125°C(Including self - temperature rise).

4.Characteristics(Reference)

