





ABIDE BY ROHS



PCB LAYOUT

使用温度范围 (Ambient temperature Range):-25°~+85°

适用线规 (Applicable Wires):AWG 22#~18#

适用基板厚度 (Applicable PCboard thickness):1.6mm

额定电压 (Voltage rating):250V AC,DC

额定电流 (Current rating):5A

接触电阻 (Contact Resistance)≤0.02 Ω

绝缘电阻 (Insulation Resistance):≥1000MΩ

耐压 (Withstand Voltange):1500VAC/min

材料 (Material)

1.基座: PA66 94V-2

2.插针: 黄铜

孔位	A-mm	B-mm
5.08-2A	10.16	5.08
5.08-3A	15.24	10.16
5.08-4A	20.32	15.24
5.08-5A	25.40	20.32
5.08-6A	30.48	25.40
5.08-7A	35.56	30.48
5.08-8A	40.64	35.56
5.08-9A	45.72	40.64
5.08-10A	50.80	45.72
5.08-11A	55.88	50.80
5.08-12A	60.96	55.88
5.08-13A	66.04	60.96
5.08-14A	71.12	66.04
5.08-15A	76.20	71.12
5.08-16A	81.28	76.20

单位 UNIT	mm	一般公差 TOLERANCE ARE				ES 浙江恩盛电子有限公司 Zhejiang Ensheng Electronics Co., Ltd.				
绘 图 DRAWN		X.°±3° X.X°±5°				WAFERA针座				
设 计 DESIGN		>0-3	>3-18	>18-50	>50-120					产品名称 TITLE
审 核 CHECKED		±0.12	±0.15	±0.3	±0.5	产品型号 MODEL	5.08-NA			
校 准 化 STANDARD		图 号 DRAWING NO	—		产品编码 PART NO	ESWF-CHOXX-L-XX-C-B				
批 准 APPROVALS		产 地 PRODUCTION			视 角 PROJ		比 例 SCALE	:	页 码 SHEET	1 OF 1

2		Wafer 针	Brass Tin 黄铜镀锡	N	
1		Housing 基座	PA66 94V-(2)	1	White 透明
序号	图号	名称	材料	数量	附注

ECN NO.	A	DATE.	NEW	CHANGE.	CHECK.	APPRO.
			DESCRIPTION.			