







ABIDE BY ROHS

| ITEM | H±0.1 |
|------|-------|
| 01   | 4.3   |
| 02   | 4.5   |
| 03   | 4.8   |
| 04   | 5.0   |
| 05   | 8.0   |
| 06   | 9.0   |
| 07   | 9.5   |
| 08   | 10.0  |
| 09   | 11.0  |
| 10   | 12.0  |
| 11   | 13.0  |
| 12   | 14.0  |
| 13   | 15.0  |
| 14   | 16.0  |
| 19   | ...   |
| 20   | 22.0  |
| 21   | 29.0  |



开关示意图



Remarks:

1. Rated current、Voltage: DC 12V 50mA
2. Contact resistance:  $\leq 30\text{m}\Omega$
3. Insulation resistance:  $\geq 100\text{M}\Omega$
4. The intensity of operations:  $260 \pm 50\text{gf}$
5. Life requirements: 100000次
6. Withstand voltage: AC 250V 1分钟
7. All materials comply with RoHS standards

|                 |           |                       |                 |                                                      |
|-----------------|-----------|-----------------------|-----------------|------------------------------------------------------|
| 5               | Button    | PPA (21H以后是聚碳材料)      | 1               | Black                                                |
| 4               | Cover     | Q195                  | 1               | Cu-Sn Plated                                         |
| 3               | Shrapnel  | SUS301                | 1               | Silver coating                                       |
| 2               | Housing   | PPA                   | 1               | Black                                                |
| 1               | Terminal  | Brass                 | 4               | Ag Plated                                            |
| NO.             | PART NAME | MATERIAL              | QTY             | FINISHING                                            |
| 单位<br>UNIT      | mm        | 一般公差<br>TOLERANCE ARE |                 |                                                      |
| 绘图<br>DRAWN     |           | X ≤ 1                 | ± 0.05          | 浙江恩盛电子有限公司<br>Zhejiang Ensheng Electronics Co., Ltd. |
| 设计<br>DESIGN    |           | 1 ≤ X ≤ 5             | ± 0.10          |                                                      |
| 审核<br>CHECKED   |           | 5 ≤ X ≤ 10            | ± 0.15          |                                                      |
| 校准化<br>STANDARD |           | X > 10                | ± 0.25          | 产品名称<br>TITLE                                        |
| 批准<br>APPROVALS |           | 图号<br>DRAWING NO      | 产品型号<br>MODEL   | 轻触开关                                                 |
|                 |           | 重量<br>WT.             | 产品编码<br>PART NO | 6*6*H插件                                              |
|                 |           | 产地<br>PRODUCTION      | 视角<br>PROJ      | ES601X-10XX-XXX-26-A                                 |
|                 |           |                       | 比例<br>SCALE     | 页码<br>SHEET                                          |
|                 |           |                       |                 | 1 OF 1                                               |