








REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	N/A		图面升级整理图面	2024.11.18	阿树
A2	ECN-P-2026041803		产品外观变更	2026.04.18	山楂




- Notes:
- Material:
 - Insulation core: Black LCP UL94V-0
 - Terminal: C1814 T=0.12mm; nickel base, gold-plated
 - Shell: Stainless steel, T=0.30mm; surface nickel-plated
 - Grounding sheet: Stainless steel, T=0.10mm
 - Card: Stainless steel, T=0.15mm
 - Main characteristics:
 - Rated current: 3A FOR VBUS;
1.25A FOR GND;
0.25A FOR OTHER.
 - Contact resistance: 40mΩ MAX
 - Insulation resistance: 100MΩ MIN
 - Withstand voltage test: 100V AC
 - Solderability: temperature 245±5 , time 5±0.5s
 - Overall insertion force: 5~20N
Overall extraction force: 8~20N
Extraction force after durability test: 6~20N
 - Service life: 10000 cycles
 - Operating temperature: -25 ~ 80

U262-241N-4BV64

- 1:AU 1U"
2:AU 3U"
5:AU 15U"
6:AU 30U"

A1	GND	B12	GND
A2	SSTXP1	B11	SSRXP1
A3	SSTXN1	B10	SSRXN1
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A10	SSRXN2	B3	SSTXN2
A11	SSRXP2	B2	SSTXP2
A12	GND	B1	GND
PIN	SIGNAL NAMF	PIN	SIGNAL NAMF

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	山楂	VIEW:	MODEL TYPE: USB TYPE C SMT-24PIN PLUG
CHECKED		UNIT: mm/in	PART NO.: U262-241N-4BV64
APPROVED		SIZE: A4	DWG NO.:

SCALE	PAGE	REVISION
N/A	1/1	A2