REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.05.09	桑 甚



规格 Specification：

1.额定值 Rating:3A 125/250VAC

2.接触电阻 Contact resistance:≤30 mΩ

3.绝缘电阻 Insulation resistance:≥100 MΩ(DC500V/Min)

4.电气寿命 Electronics life:＞10000 cycles

5.操作力 Operation force:500±150gf

6.所有材料符合Rohs要求 All meterials are Rohs compliant





PART NO.:

SS－X 03 23 S G－8 R 2 B B

① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨ ⑩ ⑪

① SS：XKB Vertical handle;

② Enclosure Material:
A－Metal case;
BLANK－Plastic case;

③ Current Rating：03－3A;

④ Switch Circuit:23－2P3T;

⑤ S：Wire bonding;

⑥ Handle Shape：G－Camber handle;

⑦ Handle Height：3~15mm;

⑧ Enclosure Shape:R－Locking rings enclosure;

⑨ Terminal specs:
1:TYPE－1；2:TYPE－2；3:TYPE－3;
4:TYPE－4；5:TYPE－5;

⑩ Handle Colour:
B－Black；W－White；R－Red

⑪ Housing Colour:
B－Black；W－White；R－Red





XKB c US
SS Series
3A 125/250VAC

产品字码标识

ANGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	

DESIGN	桑 甚	VIEW:	MODEL TYPE: SLIDE SWITCH
CHECKED		UNIT: mm/in	PART NO.: SS－0323SG－8R2BB
APPROVED		SIZE: A4	DWG NO.: X－SS－0323SG－8R2BB

SCALE	PAGE	REVISION
N/A	1/1	A0

XKB INDUSTRIAL PRECISION CO.,LIMITED