





ABIDE BY ROHS




ITEM	H	
01	7.3	√
02	7.5	



P. C. B. Layout



- Remarks:
1. Rated current, Voltage: DC 12V 50mA
 2. Contact resistance: $\leq 50\text{m}\Omega$
 3. Insulation resistance: $\geq 100\text{M}\Omega$
 4. The intensity of operations: $260\pm 50\text{gf}$
 5. Life requirements: 100000 times
 6. Withstand voltage: AC250V 1 minute
 7. All materials comply with RoHS standards



- Remarks:
1. Braiding process, can not be caused by carrying half crushed;
 2. Pay attention to the direction of the tape, with a clockwise direction out of the carrier tape, with a hole in the top or right

5	Button	PPA	1	Black
4	Cover	Q195	1	Cu-Sn Plating
3	Shrapnel	SUS	1	Ag Plating
2	Housing	PPA	1	Black
1	Terminal	Brass	4	Ag Plating
NO.	PART NAME	MATERIAL	QTY	FINISHING

单位 UNIT	mm	一般公差 TOLERANCE ARE		浙江恩盛电子有限公司 Zhejiang Ensheng Electronics Co., Ltd.	
绘图 DRAWN		$X \leq 1$	± 0.05		
设计 DESIGN		$1 \leq X \leq 5$	± 0.10	产品名称 TITLE	轻触开关
审核 CHECKED		$5 \leq X \leq 10$	± 0.15	产品型号 MODEL	12*12方头贴片
校准化 STANDARD		$X > 10$	± 0.25	产品编码 PART NO	ES1204-10XX-73X-26-B-BF
批准 APPROVALS		重量 WT.		视角 PROJ	比例 SCALE
		产地 PRODUCTION			页码 SHEET
					1 OF 1

ECN NO.	REV	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
---------	-----	-------	--------------	---------	--------	--------