








REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.07.17	桑 甚

A



A


B



PART NO.: X332C H-40-PB BL
① ② ③ ⑤ ⑥

- 1.Series No:332A-TYPE A
332B-TYPE B
332C-TYPE C
- 2.Category:H-Housing
- 3.Row No.Pin No:XX-See Table A
- 5.Material:PB-PBT
- 6.Color:Blank-Black; GR-Gray; BL-Blue

C




规格Specifications:
额定电压Voltage rating:60V AC/DC
额定电流Current rating:3A AC/DC
耐受电压Withstanding voltage:500V AC/minute
温度范围Temperature range:-40℃~+125℃
绝缘电阻Insulation resistance:≥100MΩ
接触电阻Contact resistance:≤10mΩ (测试后≤30mΩ)

TABLE A

PIN NO.	A	B	C	D
8	10.00		6.00	15.60
12	14.00	15.90	10.00	19.60
16	18.00	19.90	14.00	23.60
20	22.00	23.90	18.00	27.60
24	26.00	27.90	22.00	31.60
28	30.00	31.90	26.00	35.60
32	34.00	35.90	30.00	39.60
40	42.00	43.90	38.00	47.60

X332CH-40C-PBXX	X332CWRS-40C	X332XT-BSN	PBT UL94 V-0
X332BH-40C-PBXX	X332BWRS-40C	X332XT-BSN	PBT UL94 V-0
X332AH-40C-PBXX	X332AWRS-40C	X332XT-BSN	PBT UL94 V-0
X332CH-40-PBXX	X332CWRS-40	X332XT-BSN	PBT UL94 V-0
X332BH-40-PBXX	X332BWRS-40	X332XT-BSN	PBT UL94 V-0
X332AH-40-PBXX	X332AWRS-40	X332XT-BSN	PBT UL94 V-0
PART NO.	Suitable XKB WAFER	Suitable XKB Terminal	MATERIAL

ANGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	桑 甚
CHECKED	
APPROVED	

VIEW:
UNIT: mm/in
SIZE: A4


MODEL TYPE:
2.0mm Crimp Style Housing
PART NO.:
X332CH-40-PBBL
DWG NO.:

D


D

NO CPA FEATURE

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.07.17	桑 葚





8 PIN




12 PIN


MATED DIMENSION




8~12 PIN



16 PIN




20~40 PIN



16~40 PIN

ANGULAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



XKB INDUSTRIAL PRECISION CO.,LIMITED

DESIGN	桑 葚	VIEW:	MODEL TYPE: 2.0mm Crimp Style Housing
CHECKED		UNIT: mm/in	PART NO.: X332CH-40-PBBL
APPROVED		SIZE: A4	DWG NO.:

SCALE	PAGE	REVISION
N/A	2/3	A0



1

2


3

4



WITH CPA FEATURE



16~40 PIN



MATED DIMENSION



16~40 PIN

ANGULAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



XKB INDUSTRIAL PRECISION CO.,LIMITED

DESIGN	桑 葚	VIEW:	MODEL TYPE: 2.0mm Crimp Style Housing
CHECKED		UNIT: mm/in	PART NO.: X332CH-40-PBBL
APPROVED		SIZE: A4	DWG NO.:

SCALE	PAGE	REVISION
N/A	3/3	A0