



REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A			2025.06.19	





- SPECIFICATIONS
- Voltage rating:250V AC/DC
 - Current rating:10A AC/DC
 - Withstanding Voltage:1500V AC/minute
 - Temperature range:−40°C~+125°C
 - Insulation resistance:≥1000MΩ
 - Contact resistance:≤10mΩ
 - Material:Wafer PA66,UL94V−2
 - PIN Brass Tin−plated

PART NO.:

X5050 W V−02−N2 SN XX

Series No
Category:W−Wafer
Welding Board Angle:V−Stright 180°
Row No.Pin No:XX−02Pin
Material:N2−PA66 UL94V−2
Planting:SN−Bright Tin Plating
Color Blank−Natural Color



X5050WV−02−N2SN	Nylon 66 UL 94V−2	Brass	Tin−Plated	X5050H
PART NO	Material	Material(Pin)	Finish(Pin)	Mates With XKB Housing

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAUCES	



DESIGN		VIEW:	MODEL TYPE: 5.08mm Crimp Style Connectors
CHECKED		UNIT: mm/in	PART NO.: X5050WV−02−N2SN
APPROVED		SIZE: A4	DWG NO.: X−X5050WV−02−N2SN

XKB INDUSTRIAL PRECISION CO.,LIMITED

SCALE	PAGE	REVISION
N/A	1/3	A1