



A

A



## ■SPECIFICATIONS

- Voltage rating:250V AC/DC
- Current rating:2.5A AC/DC
- Withstanding Voltage:500V AC/minute
- Temperature range:-40°C~+125°C
- Insulation resistance:≥1000MΩ
- Contact resistance:≤20mΩ

PART NO.:



X1511 W V S-06 L HF-LP SW  
① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

- ①Series No  
②Category:W-Wafer  
③Welding Board Angle:V-Stright 180°  
④Welding Way:S-SMT  
⑤Row No.Pin No:XX-02~15Pin  
⑥Special No:L-With lock  
⑦Special No:HF-Halogen free  
⑧Material:9T-PA9T;46-PA46;LP-LCP 94V-0  
⑨Planting:SW-Matte Tin Plating

| Poles | Dimensions(mm) |       |       |
|-------|----------------|-------|-------|
|       | A              | B     | C     |
| 02    | 1.50           | 4.30  | 3.70  |
| 03    | 3.00           | 5.80  | 5.20  |
| 04    | 4.50           | 7.30  | 6.70  |
| 05    | 6.00           | 8.80  | 8.20  |
| 06    | 7.50           | 10.30 | 9.70  |
| 07    | 9.00           | 11.80 | 11.20 |
| 08    | 10.50          | 13.30 | 12.70 |
| 09    | 12.00          | 14.80 | 14.20 |
| 10    | 13.50          | 16.30 | 15.70 |
| 11    | 15.00          | 17.80 | 17.20 |
| 12    | 16.50          | 19.30 | 18.70 |
| 13    | 18.00          | 20.80 | 20.20 |
| 14    | 19.50          | 22.30 | 21.70 |
| 15    | 21.00          | 23.80 | 23.20 |



B

B



C

C



D

D

|                        |       |
|------------------------|-------|
| AuGLAR                 | ±5°   |
| X.                     | ±0.40 |
| X.x                    | ±0.30 |
| X.xx                   | ±0.20 |
| X.xxx                  | ±0.15 |
| UNSPECIFIED TOLERANCES |       |



|          |    |             |                                              |
|----------|----|-------------|----------------------------------------------|
| DESIGN   | 阿树 | VIEW:       | MODEL TYPE:<br>1.50mm Crimp Style Connectors |
| CHECKED  |    | UNIT: mm/in | PART NO.:<br>X1511WVS-06LHF-LPSW             |
| APPROVED |    | SIZE: A4    | DWG NO.:<br>X-X1511WVS-06LHF-LPSW            |